

0 601 9G4 171 – GDR 18V-200 C


Material number	0 601 9G4 171
EAN	3165140918473
1/2 L-BOXX inlay for accessories 1 600 A00 2WC	✓
1/2 L-BOXX inlay for tool and charger 1 600 A01 CU5	✓
2 x battery GBA 18V 5.0Ah 1 600 A00 2U5	✓
L-BOXX 136 1 600 A01 2G0	✓
Quick charger GAL 1880 CV 1 600 A00 B8H	✓



Technical data

Technical data

No-load speed	0-3,400 rpm
No-load speed (1st level)	0-1,100 rpm
No-load speed (2nd level)	0-2,300 rpm
No-load speed (3rd level)	0-3,400 rpm
Torque settings	3
Weight excl. battery	1.1 kg
Torque, max.	200 Nm
Impact rate	0-4,000 bpm
Impact rate (1st level)	0-2,300 bpm
Impact rate (2nd level)	0-3,400 bpm
Impact rate (3rd level)	0-4,000 bpm
Tool holder	1/4" Hex Uni
Charging time (80%/100%) approx.	30/45 min [5.0 Ah]
Battery voltage	18 V
Noise level	The A-rated noise level of the power tool is typically as follows: Sound pressure level dB(A); Sound power level dB (A). Uncertainty K= dB.



Screw diameter

Screw diameter	M 6 – M 16
----------------	------------

Sales information

Positioning

- Best combination of power and size in Bosch's 18 V category – with brushless motor

User benefit

- Excellent power-to-size ratio due to 200 Nm of torque and a head length of 126 mm
- Bluetooth Connectivity option for active tool feedback, service information, and additional control
- Equipped with a brushless motor with Electronic Motor Protection for high endurance and longer runtime