



DGE 8-32

800 watt variable high-speed straight grinder Order no. 522279

GTIN 4030293240377



- Microprocessor control with soft start, restart protection after power failure, temperature monitoring, overload protection, CDC-electronic feedback control
- 43 mm clamping neck for stationary fixing or handle attachment
- Long-neck design with hood handle for optimum handling and optimum access to hard-to-reach places
- Lightweight design for fatigue-free work
- Spindle lock
- The ideal tool for grinding, deburring, freehand milling, cutting, rust removal













Technical data

Power consumption	800 W
Voltage	230 V
Frequency	50/60 Hz
No-load speed	10600 - 32000 rpm
Max. sanding wheel diameter	50 mm
Tool holder, straight grinder	Collet
Clamping collar diameter	43 mm
Grip circumference	147 mm
Cable length	4.0 m
Dimensions WxLxH	380 x 83 x 83 mm
Weight	1.8 kg

Standard equipment

- 1 Collet (530014)
- 1 Open-ended wrench SW 17