




Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 150500 – 190000 CMA

Stud Size: 3/8

Features

Product Type Features

Terminal Features	Inspection Slot
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	3/8
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	55.491 g
----------------	----------

Contact Features

Barrel Type	Closed
Terminal Orientation	Flag
Terminal Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------



Dimensions

Wire Size	150500 – 190000 CMA
Stud Diameter	9.91 mm[.39 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	50.83 mm[2.001 in]
Barrel Inside Diameter	14.35 mm[.565 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	50
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1752680-2
HYP10 SOLIS FLAG 3/0AWG NEST

TE Part # 1752681-1
HYP10 SOLIS FLAG 1/0-4/0AWG INDENTER

Customers Also Bought

TE Part #770584-1
18P MINI UMNL PLUG HSG

TE Part #321880
TERMINAL,SOLIS R 4/0 1/2

TE Part #963598-1
MICRO-T/JPT GH66/2P

TE Part #T4111011041-000
M12 M, 4P GOLD A_CODE S SHIELDED PG7

TE Part #1-480721-0
03P CMNL PLUG HSG W/LOK NATL

TE Part #770587-1
24P MINI UMNL PLUG HSG

TE Part #33467
TERMINAL,SOLIS R 6 3/8

TE Part #T4113511041-000
M12 M, 4P GOLD D_CODE RA SHIELDED PG7

TE Part #321878
TERMINAL,SOLIS R 4/0 3/8

TE Part #4-1419106-0
VCF4-1002=CONNECTOR,HOUSING-

Documents



Product Drawings

TERMINAL,SOLIS FLAG R 3/0 3/8

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_327887_K.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_327887_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_327887_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English