



**SFP56**

TE Internal #: 2-2349201-1

zSFP+ Stacked (SFP56), Cage Assembly with Integrated Connector,  
 .6mm [.018in] Centerline, Signal

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > SFP56 Stacked Cage Assembly: EMI Spring



Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**

Centerline (Pitch): **.6 mm [ .018 in ]**

Circuit Application: **Signal**

Operating Temperature Range: **-55 – 105 °C [ -67 – 221 °F ]**

Data Rate (Max): **56 Gb/s**

[All SFP56 Stacked Cage Assembly: EMI Spring \(48\)](#)

**Features**

**Product Type Features**

Cage Type	Stacked
Pluggable I/O Product Type	Cage Assembly with Integrated Connector
Form Factor	zSFP+ Stacked (SFP56)

**Configuration Features**

Number of Positions	20
Number of Ports	24
Port Matrix Configuration	2 x 12

**Electrical Characteristics**

Data Rate (Max)	56 Gb/s
-----------------	---------

**Termination Features**

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

**Housing Features**

Centerline (Pitch)	.6 mm [.018 in]
--------------------	-----------------



### Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

### Operation/Application

Pluggable I/O Applications	SFP28
Circuit Application	Signal

### Other

Included Lightpipe	Yes
EMI Containment Feature Type	Internal/External EMI Springs

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts




TE Part # 1761394-1  
DUST COVER, SFP, GANGED & STACKED

### Also in the Series | SFP56



Pluggable I/O Cable Assemblies(17)



Pluggable IO Connectors & Cages(53)

### Customers Also Bought



TE Part #350537-1  
UMNL SOK 20-14 .0126 PTPBR



TE Part #350547-1  
UMNL PIN 20-14 PTPBR L/P



TE Part #350550-1  
UMNL SOK 20-14 PTPBR L/P



TE Part #350767-1  
03P UMNL CAP HSG V0



TE Part #350777-4  
02P UMNL PLUG HSG UL94V0



TE Part #350778-1  
02P UMNL CAP HSG



TE Part #2007394-6  
SFP+ assy2x4 Spring FingersInner LP Sn



TE Part #1-2198346-7  
zSFP+ STACKED 2X8 RECEPTACLE ASSEMBLY



TE Part #2227666-3  
ZQSFP+ STACKED, 2X1, THRU BEZEL W SPRING



TE Part #2227838-7  
2X12 ZSFP+ CONNECTOR ASSEMBLY



## Documents

### CAD Files

#### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2-2349201-1\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-2349201-1\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-2349201-1\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

#### Product Specification

English