



Grinding wheel E 125x7.2x22.23 mm Universal Line PSF STEELOX for steel/stainless steel

Grinding wheel E 125x7.2x22.23 mm Universal Line PSF STEELOX for steel/stainless steel

Item number: [62012640](#)

EAN: [4007220640883](#)

The entry-level range Universal Line PSF includes robust tools for processing the most common materials. Universal Line PSF tools achieve good results with high economic efficiency.

Grinding wheel for steel and stainless steel (INOX) with high grinding performance and good tool life.

Technical information

Abrasive	Aluminium oxide A
Dia. external	125 mm
Dia. hole	22.23 mm
Max. RPM	12200 RPM
Mounting system	Centre hole
Shape	E / 27 / T27
Width	7.2 mm

Advantages

- ✓ Suitable for general use on steel and stainless steel (INOX).
- ✓ Fast work progress and high economic efficiency thanks to the high grinding performance.
- ✓ Good tool life.
- ✓ Also suitable for low-power angle grinders. Soft grinding characteristics, achieves particularly high stock removal rates even at low contact pressure.

Materials that can be worked

- ✓ Stainless steel (INOX)
- ✓ Steel

Applications

- ✓ Chamfering
- ✓ Deburring
- ✓ Grouting
- ✓ Surface grinding
- ✓ Work on fillet welds
- ✓ Work on weld seams

Drive types

- ✓ Angle grinder
 - ✓ Drive spindle
-



August Rüggeberg GmbH & Co. KG
Hauptstraße 13
51709 Marienheide

+49 2264 9-0

+49 2264 9-400

info@pferd.com