

Product data sheet

Specifications



Repacked Roller blind push-button switch, New Unica, 6A, screwless, 2modules anthracite

NU320754W



This repacked option saves 0.319 over the standard condition

Main

Range of product	New Unica
Product or component type	Shutter control
Device presentation	Mechanism
Technology type	Electromechanical
Number of rocker	2
Device application	Control
Colour tint	Anthracite (RAL 7021)
Type of packing	Flow-pack

Complementary

Rated current	6 A
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Electrical durability	20000 cycles, cos phi = 0.6
Insulation resistance	> 5 MOhm at 500 V
Dielectric strength	2000 V
Minimum load breaking capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening distance	> 3 mm
Actuator	Rocker
Number of modules	2 modules
Connections - terminals	Screwless terminals
Cable cross section	0...2.5 mm² rigid cable 0...2.5 mm² flexible cable
Material	CuZn15: terminals Thermoplastic ABS-UV stabilised: mechanism rocker PC (polycarbonate) GF10 FR: casing PBT (polybutylene terephthalate) GF30: release button
Marking	Arrow
Surface finish	Matt
specific treatment - integrated within the material	Painted
fixing mode	Clip-in
Width	45 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	45 mm
Depth	44.35 mm
Embedding depth	32.8 mm
Product weight	0.0331 kg
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-5...50 °C
Standards	LV directive IEC 60669-1
Product certifications	CE AENOR EAC NF VDE
resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IP degree of protection	IP4X
IK degree of protection	IK04
Environmental characteristic	Oil UV resistant Acetone Liquid soap Window-cleaning fluid Petrol Alcohol Bleach

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	4.500 cm
Package 1 Length	4.510 cm
Package 1 Weight	36.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	10
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	548.000 g

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

0.3 kg CO2 eq.

Use Better



Materials and Substances

SCIP Number

C6de3800-7220-4403-a6a2-26e1f05e3f4b

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

Take-back

No


WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Technical Illustration

Wiring diagram



⚠ ⚠ DANGER

HAZARD OF ELECTRIC SHOCK, EXPLOSION, OR ARC FLASH
The product must be installed and connected by a qualified electrician.
A qualified electrician must demonstrate an in-depth knowledge of:

- Construction of electrical installations in buildings in accordance with IEC 60364
- Additional safety standards, local connection rules, and building regulations
- Standardized tools and measuring equipment

Failure to follow these instructions will result in death or serious injury.