

Eaton 259850

Catalog Number: 259850

Eaton Moeller series NZM - Molded Case Circuit Breaker. Remote operator, 208-240VAC, for size 3

General specifications



Product Name	Catalog Number
Eaton Moeller series NZM remote operator	259850
	EAN
	4015082598501
Product Length/Depth	Product Height
170 mm	140 mm
Product Width	Product Weight
140 mm	3.155 kg
Compliances	Certifications
UL/CSA	CSA (File No. 22086)
IEC	CE marking
RoHS conform	CSA (Class No. 1437-01)
	UL (File No. E140305)
	UL489
	IEC60947
	UL listed
	CSA certified
	CSA-C22.2 No. 5-09
	UL (Category Control Number DIHS)

Product specifications

Used with

NZM3(-4)

N(S)3(-4)

Type

Accessory

Remote operator, can be
synchronized

Special features

Cannot be combined with
switch-disconnector PN...
M22-CK11(20/02) dual
auxiliary switch cannot be
combined with NZM3-XR...
remote operator

Voltage rating

208 - 240 V 50/60 Hz

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Resources

Brochures

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-03_NZM3](#)

Drawings

[eaton-circuit-breaker-remote-operator-nzm-remote-operator-dimensions-004.eps](#)

[eaton-circuit-breaker-padlock-nzm-rotary-handle-dimensions.eps](#)

eCAD model

[ETN.259850.edz](#)

Installation instructions

[eaton-remote-operator-nzm3-xr-il01208006z.pdf](#)

Installation videos

[The new digital NZM Range](#)

[Introduction of the new digital circuit breaker NZM](#)

mCAD model

[DA-CS-nzm3_xr](#)

[DA-CD-nzm3_xr](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Frame

NZM3

Breaking time

1000 ms

Closing delay

80 ms

Voltage type

AC

Lifespan, mechanical

15000 operations

Number of poles

Three-pole/Four-pole

Number of operations per hour - max

60

Voltage tolerance - max

1.1

Voltage tolerance - min

.85

Rated control supply voltage (Us) at AC, 50 Hz - max

240 V

Rated control supply voltage (Us) at AC, 50 Hz - min

208 V

Rated control supply voltage (Us) at AC, 60 Hz - max

240 V

Rated control supply voltage (Us) at AC, 60 Hz - min

208 V

Rated control supply voltage (Us) at DC - max

0 V

Rated control supply voltage (Us) at DC - min

0 V

Rated operating frequency

50 Hz

Signal duration of remote operator at switch off - min

250 ms

Signal duration of remote operator at switch on - min

30 ms

Switch drive type

Motor drive

Terminal capacity (solid/flexible conductor)

18 - 14 AWG

0.75 mm² - 2.5 mm² with ferrule

Operating voltage - max

1.1 x Us

Operating voltage - min

0.85 x Us

Power consumption

350 VA (110 - 130 V AC)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia