




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **.82 – 2.08 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

--	--



Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	20.57 mm[.81 in]
Compatible Insulation Diameter Range	2.79 – 3.81 mm[.109 – .15 in]
Terminal Material Thickness	.4 mm[.015 in]
Wire Size	.82 – 2.08 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Packaging Features

Packaging Quantity	3000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on



requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2151128-2
OCEAN_2.0_Applicator-S-110F180F-RSA

TE Part # 90165-1
DAHT 250 FASTON REC 18-14 ASSY

TE Part # 7-2151128-7
OCEAN_2.0_SPARE_PART_KIT-110F180F

TE Part # 180353-2
250 FASTON,TAB,12-10 AWG,TPBR

TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp

TE Part # 2151128-1
OCEAN_2.0_Applicator-S-110F180F-RSM

TE Part # 180353-1
250 FASTON,TAB,12-10 AWG,BR

TE Part # 2238206-3
250 FASTON,FLAG,REC.,16-14 AWG,PTBR

TE Part # 60794-2
FASTIN NECESSARY?? - separate GPL: 326

TE Part # 61367-3
250 FASTON TAB 18-14 AWG TPBR


Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(116)

Insertion & Extraction Tools(6)

Insulation Boots & Sleeves(16)



Magnet Wire Terminals(1)



PCB Terminals(133)



Quick Disconnects(421)




Splices(4)


Customers Also Bought




TE Part #1746977-1
GRACE INERTIA CONNECTOR 6.2 MM PITCH 2P C




TE Part #CB5063-000
BSTS-27X25



TE Part #7-192013-1
LA1A(006)SIL



TE Part #3-350819-2
ULTRA-FAST 250 ASY REC 16-14 AWG TPBR




TE Part #1747050-3
GIC7.92 2POS PLUG HSG.BLUE




TE Part #61944-2
250 FASTON REC 18-14 AWG TPBR



TE Part #CAT-HST-ES1000
ES1000 Heat Shrink Tubing



TE Part #55621-2
TERMINAL R PG 8 1/4



TE Part #60660-1
SHUR PLUG 180 18-14 AWG TPBR

Documents

Product Drawings

250 FASTON TAB 18-14 AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_42474-4_AP.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_42474-4_AP.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_42474-4_AP.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTON Tabs](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[CSA Certificate](#)

English

[CSA Certificate](#)

English