


Cam followers



Dimensions				Basic load ratings		Fatigue load limit	Maximum radial loads		Limiting speed	Mass	Designation
D	d	B	C	dynamic C	static C ₀	P _u	dynamic F _r	static F _{0r}	r/min	kg	-
mm				kN		kN	kN				
90	30	100	35	38	76,5	9,5	160	228	1800	1,98	KR 90 PPA



Appertaining grease nipple(s)

NIP A3x9.5

Appertaining hexagonal nut

Size, mm

M 30x1.5

Rec. tightening torque, Nm

450

Internal hexagon in stud

Key width, mm

14