

Enamelled copper wire on mini bobbin
CUL 100/0,85



Advantages

Insulating varnish basis min. polyurethane, mod. current loading

Degree 1

TJ min. 155 °C

Solderable

Applications

Enamelled copper wire for the production of coils and winding and for general laboratory needs.

Approvals



Enamelled copper wire on mini bobbin **CUL 100/0,85**

Type	CUL 100/0,85	Type	CUL 100/0,85
Electrical data	Operating data		current car. cap. 2.00 A
	Environment		Heat resistance 155 °C (CL.F)
			insulating varnish min. Polyurethan, mod.
			Tin-plate >350 °C
	Measures and weights		Wire diameter 0.85 mm
			Weight 0.10 kg
			Length m (min.) 15

Subjects to change.