

Product datasheet

Specifications



Contactor, TeSys Deca Advanced,
3P(3NO), AC-3/3e, <=440V, 25A,
24...60V AC/DC coil, snap-in
terminals

LC1D25ABNE

EAN Code: 3606487539919

Main

Range of product	TeSys Deca Advanced
Product or component type	Contactor
Device short name	LC1D
Contactor application	Motor control Resistive load
Utilisation category	AC-1 AC-3 AC-3e
Poles description	3P
[Ue] rated operational voltage	Power circuit: <= 690 V AC 25...400 Hz
[Ie] rated operational current	25 A (at <60 °C) at <= 440 V AC-3 for power circuit 25 A (at <60 °C) at <= 440 V AC-3e for power circuit 40 A (at <60 °C) at <= 440 V AC-1 for power circuit
[Uc] control circuit voltage	24...60 V AC 50/60 Hz 24...60 V DC

Complementary

Motor power kW	5.5 kW at 220...230 V AC 50 Hz (AC-3) 11 kW at 380...400 V AC 50 Hz (AC-3) 11 kW at 415 V AC 50 Hz (AC-3) 11 kW at 440 V AC 50 Hz (AC-3) 15 kW at 500 V AC 50 Hz (AC-3) 15 kW at 660...690 V AC 50 Hz (AC-3) 5.5 kW at 220...230 V AC 50 Hz (AC-3e) 11 kW at 380...400 V AC 50 Hz (AC-3e) 11 kW at 415 V AC 50 Hz (AC-3e) 11 kW at 440 V AC 50 Hz (AC-3e) 15 kW at 500 V AC 50 Hz (AC-3e) 15 kW at 660...690 V AC 50 Hz (AC-3e)
Compatibility code	LC1D
Pole contact composition	3 NO
Protective cover	With
[Ith] conventional free air thermal current	40 A (at 60 °C) for power circuit 10 A (at 60 °C) for signalling circuit
Irms rated making capacity	450 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1
Rated breaking capacity	450 A at 440 V for power circuit conforming to IEC 60947

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Icw] rated short-time withstand current	240 A 40 °C - 10 s for power circuit 380 A 40 °C - 1 s for power circuit 50 A 40 °C - 10 min for power circuit 120 A 40 °C - 1 min for power circuit 100 A - 1 s for signalling circuit 120 A - 500 ms for signalling circuit 140 A - 100 ms for signalling circuit
Associated fuse rating	10 A gG for signalling circuit conforming to IEC 60947-5-1 63 A gG at <= 690 V coordination type 1 for power circuit 40 A gG at <= 690 V coordination type 2 for power circuit
Average impedance	2 mOhm - lth 40 A 50 Hz for power circuit
Power dissipation per pole	1.25 W AC-3 1.25 W AC-3e 3.2 W AC-1
[Ui] rated insulation voltage	Power circuit: 690 V conforming to IEC 60947-4-1 Signalling circuit: 690 V conforming to IEC 60947-1
Overvoltage category	III
Pollution degree	3
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947
Safety reliability level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
Mechanical durability	15 Mcycles
Electrical durability	0.9 Mcycles 40 A AC-1 at Ue <= 440 V 2 Mcycles 21 A AC-3 at Ue <= 440 V 2 Mcycles 21 A AC-3e at Ue <= 440 V
Control circuit type	AC/DC at 50/60 Hz AC/DC electronic
Coil technology	Built-in bidirectional peak limiting
Control circuit voltage limits	<= 0.1 Uc (-40...70 °C):drop-out AC/DC 0.85...1.1 Uc (-40...60 °C):operational AC 0.8...1.1 Uc (-40...60 °C):operational DC 1...1.1 Uc (60...70 °C):operational AC/DC
Inrush power in VA	15 VA 50/60 Hz (at 20 °C)
Inrush power in W	14 W (at 20 °C)
Hold-in power consumption in VA	0.9 VA 50/60 Hz (at 20 °C)
Hold-in power consumption in W	0.6 W at 20 °C
Heat dissipation	0.6 W at 50/60 Hz
Operating time	45...55 ms closing 20...90 ms opening
Maximum operating rate	3600 cyc/h at 60 °C

Connections - terminals	Control circuit: snap-in terminal 1 0.5...4 mm ² - cable stiffness: flexible without cable end Control circuit: snap-in terminal 2 0.5...4 mm ² - cable stiffness: flexible without cable end Control circuit: snap-in terminal 1 0.5...2.5 mm ² - cable stiffness: flexible with cable end Control circuit: snap-in terminal 2 0.5...2.5 mm ² - cable stiffness: flexible with cable end Control circuit: snap-in terminal 1 0.5...2.5 mm ² - cable stiffness: solid without cable end Control circuit: snap-in terminal 2 0.5...2.5 mm ² - cable stiffness: solid without cable end Power circuit: snap-in terminal 1 0.75...6 mm ² - cable stiffness: flexible without cable end Power circuit: snap-in terminal 2 0.75...6 mm ² - cable stiffness: flexible without cable end Power circuit: snap-in terminal 1 0.75...4 mm ² - cable stiffness: flexible with cable end Power circuit: snap-in terminal 2 0.75...4 mm ² - cable stiffness: flexible with cable end Power circuit: snap-in terminal 1 0.75...4 mm ² - cable stiffness: solid without cable end Power circuit: snap-in terminal 2 0.75...4 mm ² - cable stiffness: solid without cable end
Auxiliary contact composition	1 NO + 1 NC
Auxiliary contacts type	type mechanically linked 1 NO + 1 NC conforming to IEC 60947-5-1 type mirror contact 1 NC conforming to IEC 60947-4-1
Signalling circuit frequency	25...400 Hz
Minimum switching voltage	17 V for signalling circuit
Minimum switching current	5 mA for signalling circuit
Insulation resistance	> 10 MOhm for signalling circuit
Non-overlap time	1.5 ms on de-energisation between NC and NO contact 1.5 ms on energisation between NC and NO contact
Mounting support	Plate Rail

Environment

Standards	EN 60947-4-1 IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 IEC 60335-1
Product certifications	CB Scheme CCC cULus CE UKCA
IP degree of protection	IP20 front face conforming to IEC 60529
Protective treatment	TH conforming to IEC 60068-2-30
Climatic withstand	conforming to IACS E10 exposure to damp heat conforming to IEC 60947-1 Annex Q category D exposure to damp heat
Permissible ambient air temperature around the device	-40...60 °C 60...70 °C with derating
Operating altitude	0...3000 m
Fire resistance	850 °C conforming to IEC 60695-2-1
Mechanical robustness	Vibrations contactor open (2 Gn, 5...300 Hz) Vibrations contactor closed (4 Gn, 5...300 Hz) Shocks contactor closed (15 Gn for 11 ms) Shocks contactor open (8 Gn for 11 ms)
Height	110 mm

Width	45 mm
Depth	101 mm
Net weight	524 g

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.600 cm
Package 1 Width	10.100 cm
Package 1 Length	11.700 cm
Package 1 Weight	510.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	15
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.475 kg
Unit Type of Package 3	P06
Number of Units in Package 3	240
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	144.100 kg

Contractual warranty

Warranty (in months)	18
----------------------	----

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Total lifecycle Carbon footprint	13
Environmental Disclosure	Product Environmental Profile

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	7d699774-c34b-4bf4-9ecb-388a149eefdd
REACH Regulation	REACH Declaration

Use Longer

 Lifetime extension	
Repair	No

Use Again

 Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Technical Illustration

Assembly's dimensions

