

Eaton 135583

Catalog Number: 135583

Eaton Moeller® series E58 Diffuse reflective sensor, Sn=610mm, 4L, 10-30VDC, NPN, PNP, M18, insulated material, line 2m 13100R6517

General specifications



Product Name

Eaton Moeller® series E58 Diffuse reflective sensor

Catalog Number

135583

EAN

4015081323760

Product Length/Depth

152.4 mm

Product Height

44.45 mm

Product Width

152.4 mm

Product Weight

0.23 kg

Certifications

CSA-C22.2 No. 14

UL Category Control No.: NRKH, NRKH7

CE

UL File No.: E117028

CSA

UL 508

IEC/EN 60947-5-2

CSA File No.: 50513

UL

CSA Class No.: 3211-07

Product specifications

Type

Optical sensors

Features

Right-angled beam

Electric connection type

Cable

Enclosure material

Plastic

Enclosure type

Cylinder, screw-thread

Operating mode

Switching principle: Adjustable bright/dark switching

Explosion safety category for dust

None

Explosion safety category for gas

None

Functions

Protection against polarity reversal

Short-circuit protection

Reflected-light beam

Voltage type

DC

Wire size

22

Connection type

2 m connection cable

4-wire

Cable sheath material

Polyvinyl chloride (PVC)

Light type

Infrared light

Degree of protection

IP67

NEMA 6

Interface type

Other

Resources

Catalogs

Product Range Catalog Sensors – products, basic information, applications

Declarations of conformity

DA-DC-00004652.pdf

DA-DC-00004657.pdf

Drawings

eaton-proximity-switches-dimensions-002.eps

eaton-proximity-switches-dimensions-004.eps

eaton-proximity-switches-3d-drawing-006.eps

Installation instructions

IL05305002Z

mCAD model

DA-CD-90_28267_005

DA-CS-90_28267_005

LED indicator

Status indication of Switching state: Red LED

Switch function type

Other

Load current

Max. 250 mA (Ie, NPN, 120 > 50°C)

Max. 100 mA (Ie, PNP)

Laser protection class

None

Operation agent-safety class

Safety class 2

Shock resistance

100 g, Mechanical, Shock duration 3 ms

Optical surface material

Plastic

Output current (mA) - max

250 mA

Output current at protected output - max

0 mA

Rated control supply voltage (Us) at AC, 50 Hz - max

0 V

Rated control supply voltage (Us) at AC, 50 Hz - min

0 V

Rated control supply voltage (Us) at AC, 60 Hz - max

0 V

Rated control supply voltage (Us) at AC, 60 Hz - min

0 V

Rated control supply voltage (Us) at DC - max

30 V

Rated control supply voltage (Us) at DC - min

10 V

Rated switching distance (Sn)

610 mm

Reflector distance - min

0 mm

Sensor height

0 mm

Sensor length

65 mm

Switching distance - max

610 mm

Switching voltage of OSSD at state high

0 V

Transmission range of the safety field

0 m

Voltage rating - max

30 V

Safety type (IEC 61496-1)

1

Switching frequency

500 Hz

Sensing mode

Light-/dark switching

Switching output type

PNP/NPN

Sensor material

Insulated material

Wavelength of the sensor

0 nm

Width sensor

0 mm

Product category

Comet Series

Response time

1 ms

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-40 °C

Diameter sensor

18 mm

Light dot size

0 mm²

Number of contact energized outputs with signalling function

0

Number of outputs (protected contact energized)

0

Number of outputs (protected semiconductor)

0

Number of outputs (semiconductor with signaling function)

2

Operating distance - max

0 mm

Operating distance - min

0 mm

Operational current (Ib) in the switched state at 24 V DC

30 A

Adjustment type

Manual adjustment



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia