

# 9001BW246

## CONTROL STATION Ø30 Standard Duty Momentary Pushbuttons Mushroom 1NO-1NC


[Download your 9001BW246 datasheet](#)

[Characteristics](#) | [Documents & Downloads](#)

### Main

☐ Hide

Range of product	Harmony 9001BW
Product or component type	Complete control station
Device short name	9001BW
Control station application	Two functions
Colour of base of enclosure	Grey

### Complementary

☐ Hide

Material	Cast aluminium
Cable entry	1 entry for 1/2" - 14 NPT
CAD overall width	70 mm
CAD overall height	108 mm
CAD overall depth	91 mm
Type of operator	Momentary
Control station composition	1 mushroom head Ø 30 mm push-button, cap/operator or lens colour:black (START marking)white 1 mushroom head Ø 30 mm push-button, cap/operator or lens colour:black (STOP marking)white
Contacts type and composition	1 NO + 1 NC
Mechanical durability	5000000 cycles
Connections - terminals	Screw-clamp terminal
[Ie] rated operational current	0.6 A at 600 V - utilisation category AC-1/DC-1 0.75 A at 480 V - utilisation category AC 1.5 A at 240 V - utilisation category AC 3.75 A at 120 V - utilisation category AC
Device mounting	Surface
Type of installation	Indoor/outdoor



### Environment

☐ Hide

Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
NEMA degree of protection	NEMA 1 NEMA 4
Standards	EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 EN/IEC 60947-5-5 JIS C 4520 UL 508 CSA C22.2 No 14
Product certifications	CSA UL listed
Environmental characteristic	Waterproof Dustproof

Offer Sustainability

 Hide

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available  <a href="#">download Product environmental</a>
Product end of life instructions	Available  <a href="#">download End of life manual</a>