


short-stroke cylinder ADVC-50-20-I-P-A

Part number: 188262

★ Core product range

FESTO



Data sheet

Feature	Value
Stroke	20 mm
Piston diameter	50 mm
Based on the standard	ISO 6431 Hole pattern VDMA 24562
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Mode of operation	double-acting
Design structure	Piston Piston rod
Position detection	For proximity sensor
Operating pressure	0.6 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-20 ... 80 °C
Theoretical force at 6 bar, return stroke	1,057 N
Theoretical force at 6 bar, advance stroke	1,178 N
Moving mass	123 g
Product weight	665 g
Mounting type	Optional with through hole with accessories
Pneumatic connection	G1/8
Materials note	Free of copper and PTFE
Material cover	Wrought Aluminium alloy Anodised
Material seals	TPE-U(PU)
Material housing	Wrought Aluminium alloy Anodised
Material piston rod	High alloy steel