

# Geocel® ROOFERS MATE

## WET OR DRY SURFACE SEALANT

**Geocel® Roofers Mate**, wet or dry surface sealant is a single component, high performance elastomeric sealant and can be used for most roofing applications and repairs. It will adhere to various roofing substrates including lead, bitumen and galvanised steel. Ideal for sealing around gutters, down pipes, lead flashing and corrugated roofing.

- Excellent adhesion to most common roofing substrates
- One component, easy to apply and tool
- Suitable for use on damp and wet surfaces
- Cures to form a flexible seal with high movement capability
- Mildew resistant
- High gloss finish
- Can be overpainted

### SPECIFICATIONS

Manufactured under ISO 9001



## TECHNICAL DATA

|                            |   |
|----------------------------|---|
| <b>Storage Life</b>        | 12 months from date of manufacture when stored in temperatures below 30°C |
| <b>Colour</b>              | Black, Grey   |
| <b>Tack Free Time</b>      | 72 hours  |
| <b>Cure Rate</b>           | 5 days (6mm bead)   |
| <b>Specific Gravity</b>    | 0.95  |
| <b>Tensile Strength</b>    | 2.0Mpa  |
| <b>Elongation</b>          | 800%  |
| <b>Service Temperature</b> | -40°C to +80°C  |

Specification writers: These values are not intended for use in preparing specifications. Please contact your local **Geocel® Sales Representative** prior to writing specifications on this product.

## APPLICATION

Ensure gaps and cracks to be filled are free from dust, dirt and grease. Remove nozzle and cut off end of cartridge. Replace nozzle and cut the tip to the required width. Place the cartridge in a cartridge gun and apply material into gap and crack to be filled. Ensure **Geocel® Roofers Mate** makes full contact with the sides and back of the joint.

## FINISHING

When applied to wet surfaces tooling is necessary to ensure that a good bond with the surface is formed. Always tool down immediately following application using a spatula or a piece of wood wetted with a dilute soap solution.

## CLEAN UP

Excess sealant may be cleaned off whilst in an uncured state using a dry disposable cloth. Alcohol based solvents can be used to clean tools.

## PAINTING

**Geocel® Roofers Mate** sealant may be painted after 24 hours, some paints may crack in dynamic joints. Please see paint manufacturer's specifications.

## LIMITATIONS

**Geocel® Roofers Mate** is not suitable for surfaces that bleed oils or plasticisers. It should be ensured that the sealant is compatible with the substrates to which it is being applied.

## PACKAGING

**Geocel® Roofers Mate** is supplied in 310ml cartridges packed in boxes of 12.

## HEALTH AND SAFETY

Health and Safety data sheets available on request.

## TECHNICAL SERVICE

For further technical information, advice on suitability for specific applications, or detailed Health and Safety information, contact **Geocel® Technical Service**.

**IMPORTANT NOTE** The information contained herein is offered in good faith and is believed to be accurate. However, because conditions and methods of use of our products are beyond our control, this information should not be used in substitution for customer's tests to ensure that Geocel's products are safe, effective and fully satisfactory for the intended end use. Suggestions of use shall not be taken as inducements to infringe any patent.

Geocel's sole warranty is that the product will meet the Geocel sales specifications in effect at the time of shipment.

Your exclusive remedy for breach of such warranty is limited to refund of purchase price or replacement of any product shown to be other than as warranted.

Geocel specifically disclaims any other express or implied warranty of fitness for a particular purpose or merchantability.

Geocel disclaims liability for any incidental or consequential damage.

# Geocel®

Geocel Limited

Western Wood Way, Langage Science Park, Plympton, Plymouth, Devon, PL7 5BG

Tel: 01752 334350 Fax: 01752 202065 Email: [info@geocel.co.uk](mailto:info@geocel.co.uk)

[www.geocel.co.uk](http://www.geocel.co.uk)