

SPECIFIC HAND TRUCKS



10
ANS

250 KG

Bin liners

Range designed to pick up a bin at an ergonomic height without having to bend down thanks to the adjustable attachment. Ideal for order picking or transporting small bulk loads in a bin.

- Designed for 300 x 400 mm bins. Stacking of up to 8 bins possible
- Welded frame with a load capacity of up to 250 kg.
- Model with closed handles: equipped with star wheels suitable for climbing stairs or pavements, delivered with a scratch strap.
- Model with puncture-proof wheels: optimised rolling up to 150 kg.
- Bin holder accessories: Ø 25 mm tube without sharp corners, height adjustable without tools by means of a butterfly screw, foldable for use as a classic trolley. Designed for a load of 70 kg.
- Delivered assembled.

If you already have a hand truck (signature model 250 or 350 kg), only the option for bins 812 005 508 is required.



810 005 346

Reference	Handles	Wheels	Ø Wheels	Accessory	Overall dimensions mm	Weight
810 005 346	On guard	CC	250	Min/max height: 150/750 Installation area: 520 x 315	610 x 745 x 1170	18
810 005 347		PN	260		610 x 750 x 1170	16
810 005 348		IN	160 x 3		610 x 790 x 1216	21
810 005 349	Closed	CC	160 x 3			

CC: rubber, PN: pneumatic, IN: puncture proof

PRODUCT ZOOM



810 005 347 / 810 005 348



810 005 349
Model with closed handles
equipped with a Velcro strap.