

Crimp Information Sheet

Terminal Part Number: 13881788
 Surface Plating: SN
 Material Thickness [mm]: 0,21
 Cross Section [mm²]: 0,75

*This document is non-contractual
 and for information only.
 For more information, please
 consult your local sales office*

Cable Type codes: 2010
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 1,60 - 1,90
 Seal(s): NONE

| Cable type / seal | Arrangement | Nominal Insul. diam [mm] | Tear-out force [N] | CCH [mm] | Tol CCH [mm] | CCW [mm] | Tol CCW [mm] | ICH [mm] | Tol ICH [mm] | ICW [mm] | Tol ICW [mm] |
|-------------------|-------------|--------------------------|--------------------|----------|--------------|----------|--------------|----------|--------------|----------|--------------|
| 2010 0,75 | | 1,75 | 90 | 1,05 | 0,05 | 1,77 | 0,10 | 2,00 | 0,10 | 2,00 | 0,10 |

Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR (AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B

Industry Designator: DIN

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE, XLPE/PVDF, XLPVC

Insul. Wall Designator: THIN

