

M18 ONEFHIWF1D-121C

M18 FUEL™ ONE-KEY™ 1" HIGH TORQUE D-HANDLE IMPACT WRENCH WITH FRICTION RING AND EXTENDED ANVIL

The M18 FUEL™ D-handle high torque impact wrench with a 150 mm extended anvil delivers 2576 Nm of fastening torque replacing AC, petrol or pneumatic solutions

Delivers up to 2711 Nm of nut-busting torque that enables bolts up to M42 to be unfastened

The 4 -Mode DRIVE CONTROL allows the user to shift into four different speed and torque settings to maximise application versatility

The integrated blow counting sensor enhances the consistent repeatability of the chosen torque setting

ONE-KEY™ tool tracking & security offers a free of charge cloud-based tracking network and inventory management platform for your tools.

ONE-KEY™ also features a remote locking functionality. Customisation function allows for precise tool adjustment to application

Lug nut mode when enabled through ONE-KEY™ will automatically shut the tool off when it comes into the range of 475 Nm - 610 Nm to prevent over-tightening of lug nuts

Tri-LEDs deliver high definition lighting to increase workspace visibility

The HIGH OUTPUT™ system of tools elevates the M18 FUEL™ technologies to a new level and delivers extended performance and extended run time. These tools are designed to maximise the partnership with HIGH OUTPUT™ and FORGE™ batteries



REDLITHIUM™



No load speed (rpm)	600 / 700 / 900 / 1200
Impact rate (ipm)	750/ 930/ 1,200/ 1,440
Nut busting torque [Nm]	2,711
Weight with battery pack (EPTA) (kg)	12.7 (M18 FB12)
Kit included	1 x M18 FB12 Battery pack, M12-18 FC Charger, Kitbox
Article number	4933499251