


Eaton 087918

Catalog Number: 087918

Eaton Moeller® series RMQ16 Illuminated pushbutton actuator, red, maintained Q18LTR-RT

General specifications



Product Name

Eaton Moeller® series RMQ16
Illuminated pushbutton actuator

Catalog Number

087918

EAN
4015080879183

Product Length/Depth

59 mm

Product Height

18 mm

Product Width

18 mm

Product Weight

0.009 kg

Certifications

CSA-C22.2 No. 14-05
UL
UL Category Control No.: NKCR
CSA File No.: 46552
IEC/EN 60947
IEC/EN 60947-5
UL File No.: E29184
CE
UL 508
CSA
CSA Class No.: 3211-03

Catalog Notes

Filament bulb or LED needs to be
ordered separately

Product specifications

Type

Illuminated pushbutton actuator

Actuator color

Red

Actuator function

Maintained

Switching function latching

10.10 Temperature rise

Not applicable.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Please enquire

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

Resources

Catalogs

[eaton-rmq-titan-brochure-br047004en-en-us.pdf](#)

[eaton-pushbuttons-signal-towers-sensors-assortment-overview-catalog-ca047003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-00004158.pdf](#)

[DA-DC-00004136.pdf](#)

Drawings

[eaton-operating-pushbutton-rmq16-dimensions-002.eps](#)

[eaton-operating-button-rmq16-symbol-002.eps](#)

eCAD model

[ETN.087918.edz](#)

Installation instructions

[IL04716016Z](#)

mCAD model

[DA-CS-druck_18](#)

[leuchtdruck_18.stp](#)

[DA-CD-druck_18](#)

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Operating frequency

1800 Operations/h

Pollution degree

3

Climatic proofing

Damp heat, constant, to IEC 60068-2-78

Damp heat, cyclic, to IEC 60068-2-30

Connection to SmartWire-DT

No

Actuating force

4 N

Ambient operating temperature - max

60 °C

Ambient operating temperature - min

-25 °C

Ambient operating temperature (enclosed) - max

40 °C

Ambient operating temperature (enclosed) - min

25 °C

Equipment heat dissipation, current-dependent P_{vid}

0 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

0 W

Number of command positions

1

Opening diameter

16 mm

Opening height

0 mm

Rated insulation voltage (U_i)

250 V

Rated operational current for specified heat dissipation (I_n)

0 A

Rated operational voltage (U_e) at AC - max

24 V

Rated impulse withstand voltage (U_{imp})

800 V AC

Bezel color

Black

Shock resistance

Mechanical, According to IEC/EN 60068-2-27

40 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal

shock 11 ms

Bezel material

Plastic

Terminal capacity

0.5 - 1.0 mm²

Design

Flat

Mounting position

As required

Terminal size

2.8 x 0.8 mm to DIN 46247 and IEC 60760, Fast-on connectors

2.8 x 0.8 mm to DIN 46244, Blade terminal

Overvoltage category

III

Control circuit reliability

1 failure per 10,000,000 switching operations (Statistically determined, at 24 V DC/5 mA)

1 failure per 5,000,000 switching operations (statistically determined, at 5 V DC/1 mA)

Degree of protection

NEMA 1

IP65

Degree of protection (front side)

IP65

NEMA 1

Inscription

Blank

Front element type

Flat

Lens type

Square

Lifespan, mechanical

30,000,000 Operations

Static heat dissipation, non-current-dependent Pvs

0 W

Width opening

0 mm

Product category

RMQ16

Size

Front dimensions: 18 x 18 mm

Suitable for

Illumination



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)