

Neodymium Deep Pot Bi-pole Magnet datasheet

- Neodymium iron boron 'rare earth' material
- Strongest magnet material available
- 80°C max. operating temp. (unless stated)
- N35 grade (Nickel plated)
- Custom designs available
- Aluminium pot
- Mild steel pole pieces



Product Information

Product No.	Diameter <i>mm</i>	Height	Thread size	Weight <i>kg</i>	Pull force
NH025	12.7	12	M5	0.01	2.5
NH065	16	16	M6	0.018	8.0
NH130	22.2	20	M6	0.04	16.0
NH240	25.4	25	M6	0.07	25.0