

Technical data


2213SC3

Double-row self-aligning ball bearings



Self-aligning ball bearing, pressed steel cage, open

VISUAL (S)



PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	65 mm
D - External diameter	120 mm
B - Bearing/Inner ring width	31 mm
rs - Min fillet radius	1,5 mm
Radial clearance class	C3
Precision class	P0
Mass	1,5 kg

PRODUCT PERFORMANCE	
C - Dynamic load	43500000 mN
C0 - Static load	16400000 mN
Cu - Fatigue limit load	920000 mN
e - Coefficient	0.28
Y0 - Static axial load coefficient	2.4
Y1 - Lower axial load coefficient	2.3
Y2 - Upper axial load coefficient	3.5
N lim - Oil lubrication limit speed	36000 °/s
N lim - Grease lubrication limit speed	28800 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT	
da min - Min shoulder diameter IR	73 mm
Da max - Max shoulder diameter OR	112 mm



ABUTMENT	
ra max - Max shaft & housing fillet radius	1,5 mm