

(CUSTOMER DRAWING) 顧客用図面

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,1997.

© COPYRIGHT 1997

BY AMP INCORPORATED,ALL RIGHTS RESERVED.



LOC
J

DIST




REVISIONS

変更

P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
		SEE 1 OF 2				




5,8,9-1123309-2;AS SHOWN
SEQUENTIAL TYPE



	回路番号
	1 2
B 列	① Signal ② Ground
A 列	③ Signal ④ Signal

POINT OF SEQUENTIAL



NOTES

- MATERIAL:HOUSING:GLASS FILED THERMO PLASTIC
POLYESTER(94V-0),COLOR:BLACK
TAB CONTACT:COPPER ALLOY
RETENTION LEG:BRASS
- FINISH(CONTACT AREA):0.38μmMIN GOLD PLATING
OVER Ni PLATING
- FINISH(CONTACT AREA):0.76μmMIN GOLD PLATING
OVER Ni PLATING
- FINISH(RETENTION LEG): TIN PLATED
(CONTACT TAIL) OVER NICKEL
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

注記

- 材料:ハウジング:ガラス入り熱可塑性
ポリエステル樹脂(94V-0),色:黒
タブコンタクト:銅合金
リテンションレグ:黄銅
- めっき:コンタクト:全面Ni下地
接触部:0.38μm MIN金めっき
- めっき:コンタクト:全面Ni下地
接触部:0.76μm MIN金めっき
- めっき:リテンションレグとコンタクト半田付部
ニッケル下地の上にスズめっき

XY	④ ②	5-1123309-2	⑤ OBSOLETE
YY	④ ②	9-1123309-2	
XX	④ ②	8-1123309-2	
KEY TYPE	コンタクトのめっき (FINISH)	製品番号 (PART NO.)	

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN K.KIKEDA 7/NOV/97	WIRE RANGE 総合電線断面積		INSULATION DIA 絶縁外径	
DIMENSIONS: 単位 寸 mm		CHK N.MATSUBARA 26 NOV '97	tyco Electronics			
TOLERANCES UNLESS OTHERWISE SPECIFIED		APVD S.MANABE 10 DEC '97	Tyco Electronics AMP K.K Kawasaki,Japan			
一般公差 1mm : ±0.3 3mm : ±0.35 10mm : ±0.4 ANGLE : ±3°		PRODUCT SPEC 108-5453	NAME 2列 ヘッダーアセンブリー 4P			
MATERIAL 材料		APPLICATION SPEC 114-5246	DOUBLE ROW HEADER ASS'Y 4P("H"TYPE) <DYNAMIC D-5200 D>			
FINISH 仕上		WEIGHT	DRAWING NO C=1123309			
注記参照 SEE NOTE		CUSTOMER DRAWING	SIZE A3			
			CAGE CODE 00779			
			SCALE 1-1			
			SHEET 2 OF 2			
			REV C1			