





Swivel Black Castor, 50mm Black Rubber, 40kg

Design Black castor

PRODUCT

Article number	366 510	366520	346510	346520
				

Product Details

Castor assembly : Pressed steel, plate or threaded stem fitting, black epoxy paint.

Swivel : Swivel on two rows of balls

Rim : Black Polypropylene.

Tread : Black Rubber. Non-marking.

Hub : Plain bearing. Black steel threadguards.

Specifications	Plate	Threaded Stem
Wheel Diameter - ØD ± 1%	50 mm	50 mm
Hub Type	Plain bore	Plain bore
Hub Length	21 mm ±1	21 mm ±1
Width of Tread	18mm ±1	18 mm ±1
Width of Tread-on floor	18 mm ±1	18 mm ±1
Overall Height	72 mm	69 mm
Offset	23 mm	23 mm
Fixing Plate Dimensions	42x42 mm	-
Fixing Centres	32x32 mm	-
Fixing Hole Size	4,5 mm	M 10x20 mm
Hardness of tread A ±3	A 80° Shore	A 80° Shore
Load capacity	40 Kg	40 Kg
Temperature	-5 / +50 °C	-5 / +50 °C

TECHNICAL DATA

Applications :

Appliances and furniture.

Without light reflection.

Abrasion resistant.

Easy to move.