


Microwave MLC's

AQ Series



These porcelain and ceramic dielectric multilayer capacitor (MLC) chips are best suited for RF/Microwave applications typically ranging from 10 MHz to 4.2 GHz. Characteristic is a fine grained, high density, high purity dielectric material impervious to moisture with heavy internal palladium electrodes.

These characteristics lend well to applications requiring:

- 1) high current carrying capabilities;
- 2) high quality factors;
- 3) very low equivalent series resistance;
- 4) very high series resonance;
- 5) excellent stability under stresses of changing voltage, frequency, time and temperature.

MECHANICAL DIMENSIONS: inches (millimeters)

Case	Length (L)	Width (W)	Thickness (T)	Band Width (bw)
AQ06	.063±.006 (1.60±.152)	.032±.006 (.813±.152)	.035 Max. (.889)	.014±.006 (.357 ±.152)
AQ11	.055±.015 (1.40±.381)	.055±.015 (1.40±.381)	.020/.057 (.508/1.45)	.010 + .010 -.005 (.254 +.254 -.127)
AQ12	.055 + .015 - .010 (1.40+ .381 - .254)	.055±.015 (1.40±.381)	.020/.057 (.508/1.45)	.010 + .010 -.005 (.254 +.254 -.127)
AQ13	.110±.020 (2.79±.508)	.110±.020 (2.79±.508)	.030/.102 (.762/2.59)	.015±.010 (.381±.254)
AQ14	.110 + .020 - .010 (2.79 +.889 -.254)	.110±.010 (2.79±.508)	.030/.102 (.762/2.59)	.015±.010 (.381±.254)

*For Tape and Reel packaging details see page 88

HOW TO ORDER

AQ

AVX Style
AQ06, AQ11,
AQ12, AQ13,
AQ14

11

Case Size
(See Chart)

E

Voltage Code

5 = 50V
1 = 100V
E = 150V
2 = 200V
V = 250V
9 = 300V
7 = 500V

M

Temperature Coefficient Code

M = +90±20ppm/°C (AQ06/11/12/13/14)
A = 0±30ppm/°C (AQ11/12/13/14)
C = 15% ("J" Termination only) (AQ12/14)

100

Capacitance

EIA Capacitance Code in pF.
First two digits = significant figures or "R" for decimal place.
Third digit = number of zeros or after "R" significant figures.

J

Capacitance Tolerance Code

A = ±.05 pF
B = ±.1 pF
C = ±.25 pF
D = ±.5 pF
F = ±1%
G = ±2%
J = ±5%
K = ±10%
M = ±20%
N = ±30%

A

Failure Rate Code
A = Not Applicable

1

Termination Style Code

1 = Pd/Ag (AQ11/13 only)
7 = Ag/Ni/Au (AQ11/13 only)
J = Nickel Barrier Sn/Pb (60/40) - (AQ06/12/14 only)

ME

Packaging* Code

3A = 13" Reel (AQ06 only)
6A = Waffle Pack (AQ06 only)
ME = 7" Reel
RE = 13" Reel
WE = Waffle Pack
1A = 7" Reel (AQ06 only)

PACKAGING

Standard Packaging = Waffle Pack (for T&R packaging see page 88)
AQ11/12 maximum quantity per waffle pack is 100.
AQ13/14 maximum quantity is 80.



ELECTRICAL SPECIFICATIONS

AQ06, AQ11, AQ12, AQ13, AQ14		
	M & A	C
Temperature Coefficient	(M) +90 ±20PPM/°C and (A) 0 ±30PPM/°C	±15%
Capacitance Range	0.1 pF to 5100 pF	0.001µF to 0.1µF
Capacitance Tolerance	±0.1 pF to ±20%	±10%, ±20%, ±30%
Operating Temperature	-55°C + 125°C	-55°C to +125°C
Quality Factor or Dissipation Factor	Per MIL-PRF-55681/4	2.5% @ 1kHz
Insulation Resistance	Per MIL-PRF-55681 10 ⁶ megohm to 470 pF @ +25°C 10 ⁵ megohm to 470 pF @ +125°C 10 ⁶ megohm above 470 pF @ +25°C 10 ⁴ megohm above 470 pF @ +125°C	10 ⁴ megohm min @ 25°C & R VDC 10 ³ megohm min @ 25°C & R VDC
Aging	None	<3% per decade hour
Piezoelectric Effects	None	None
Dielectric Withstanding Voltage	2.5 x rated voltage (for 500V rated 1.5 x rated voltage)	2.5 x rated voltage (for 500V rated 1.5 x rated voltage)

ENVIRONMENTAL CHARACTERISTICS

Will meet or exceed performance characteristics as outlined in MIL-PRF-55681/4.

REQUIREMENT	MIL-STD-202 METHOD
Life	108, Condition F
Shock	213, Condition J
Vibration	204, Condition B
Immersion	104, Condition B
Salt Spray	101, Condition B
Solderability	208
Thermal Shock	107, Condition B
Terminal Strength	211
Temperature Cycling	102, Condition C
Moisture Resistance	106
Barometric Pressure	105, Condition B
Resistance to Soldering Heat	210, Condition C

QUALITY FACTOR vs. FREQUENCY (Typical)

Capacitance	@ 30 MHz	@ 150 MHz	@ 500 MHz	@ 1000 MHz
1 pF	30000	4000	800	350
10 pF	9000	2000	400	150
30 pF	5000	800	200	60
100 pF	2800	400	70	25
200 pF	1500	250	40	12

CAPACITANCE AND SIZE vs. SERIES SELF RESONANT FREQUENCY (Typical)

DIMENSIONS: inches (millimeters)

Case	Size (Nominal)	1 pF	10 pF	50 pF	100 pF
AQ06	.063 x .032 x .035 (1.60 x .813 x .889)	9.6 GHz	3.2 GHz	1.5 GHz	1.0 GHz
AQ11/12	.055 x .055 x .057 (1.40 x 1.40 x 1.45)	9.6 GHz	3.2 GHz	1.5 GHz	1.0 GHz
AQ13/14	.110 x .110 x .102 (2.79 x 2.79 x 2.59)	6.4 GHz	2.2 GHz	1.0 GHz	0.7 GHz

Microwave MLC's



AQ Series Available Capacitance/Size/WVDC/T.C.

TABLE I: TC: M (+90±20PPM/°C)
CASE SIZE 06, 11, 12, 13 & 14

DIMENSIONS: inches (millimeters)

Case	Length	Width	Thickness	Band Width	Avail. Term.
06	.063±.006 (1.60±.152)	.032±.006 (.813±.152)	.035 Max. (.889)	.014±.006 (.357 ±.152)	J
11	.055±.015 (1.40±.381)	.055±.015 (1.40±.381)	.020/.057 (.508/1.45)	.010 +.010 -.005 (.254 +.254 -.127)	1 & 7
12	.055±.025 (1.40±.635)	.055±.015 (1.40±.381)	.020/.057 (.508/1.45)	.010 +.010 -.005 (.254 +.254 -.127)	J
13	.110±.020 (2.79±.508)	.110±.020 (2.79±.508)	.030/.102 (.762/2.59)	.015±.010 (.381±.254)	1 & 7
14	.110 +0.035 -0.020 (2.79 +.889 -.508)	.110±.020 (2.79±.508)	.030/.102 (.762/2.59)	.015±.010 (.381±.254)	J

Case: AQ06			Case: AQ11, AQ12			Case: AQ13, AQ14					
Cap. pF	Cap. Tol.	WVDC	Cap. pF	Cap. Tol.	WVDC	Cap. pF	Cap. Tol.	WVDC	Cap. pF	Cap. Tol.	WVDC
0.1	B	250	0.1	B	150	0.1	B	500	100	F, G, J, K, M	500
0.2	B	250	0.2	B	150	0.2	B	500	110	F, G, J, K, M	300
0.3	B,C	250	0.3	B,C	150	0.3	B,C	500	120	F, G, J, K, M	300
0.4	B,C	250	0.4	B,C	150	0.4	B,C	500	130	F, G, J, K, M	300
0.5	B, C, D	250	0.5	B, C, D	150	0.5	B, C, D	500	150	F, G, J, K, M	300
0.6	B, C, D	250	0.6	B, C, D	150	0.6	B, C, D	500	160	F, G, J, K, M	300
0.7	B, C, D	250	0.7	B, C, D	150	0.7	B, C, D	500	180	F, G, J, K, M	300
0.8	B, C, D	250	0.8	B, C, D	150	0.8	B, C, D	500	200	F, G, J, K, M	300
0.9	B, C, D	250	0.9	B, C, D	150	0.9	B, C, D	500	220	F, G, J, K, M	200
1.0	B, C, D	250	1.0	B, C, D	150	1.0	B, C, D	500	240	F, G, J, K, M	200
1.1	B, C, D	250	1.1	B, C, D	150	1.1	B, C, D	500	270	F, G, J, K, M	200
1.2	B, C, D	250	1.2	B, C, D	150	1.2	B, C, D	500	300	F, G, J, K, M	200
1.3	B, C, D	250	1.3	B, C, D	150	1.3	B, C, D	500	330	F, G, J, K, M	200
1.4	B, C, D	250	1.4	B, C, D	150	1.4	B, C, D	500	360	F, G, J, K, M	200
1.5	B, C, D	250	1.5	B, C, D	150	1.5	B, C, D	500	390	F, G, J, K, M	200
1.6	B, C, D	250	1.6	B, C, D	150	1.6	B, C, D	500	430	F, G, J, K, M	200
1.7	B, C, D	250	1.7	B, C, D	150	1.7	B, C, D	500	470	F, G, J, K, M	200
1.8	B, C, D	250	1.8	B, C, D	150	1.8	B, C, D	500	510	F, G, J, K, M	150
1.9	B, C, D	250	1.9	B, C, D	150	1.9	B, C, D	500	560	F, G, J, K, M	150
2.0	B, C, D	250	2.0	B, C, D	150	2.0	B, C, D	500	620	F, G, J, K, M	150
2.2	B, C, D	250	2.2	B, C, D	150	2.2	B, C, D	500	680	F, G, J, K, M	150
2.4	B, C, D	250	2.4	B, C, D	150	2.4	B, C, D	500	750	F, G, J, K, M	150
2.7	B, C, D	250	2.7	B, C, D	150	2.7	B, C, D	500	820	F, G, J, K, M	150
3.0	B, C, D	250	3.0	B, C, D	150	3.0	B, C, D	500	910	F, G, J, K, M	150
3.3	B, C, D	250	3.3	B, C, D	150	3.3	B, C, D	500	1000	F, G, J, K, M	150
3.6	B, C, D	250	3.6	B, C, D	150	3.6	B, C, D	500			
3.9	B, C, D	250	3.9	B, C, D	150	3.9	B, C, D	500			
4.3	B, C, D	250	4.3	B, C, D	150	4.3	B, C, D	500			
4.7	B, C, D	250	4.7	B, C, D	150	4.7	B, C, D	500			
5.1	B, C, D	250	5.1	B, C, D	150	5.1	B, C, D	500			
5.6	B, C, D	250	5.6	B, C, D	150	5.6	B, C, D	500			
6.2	B, C, D	250	6.2	B, C, D	150	6.2	B, C, D	500			
6.8	B, C, J, K, M	250	6.8	B, C, J, K, M	150	6.8	B, C, J, K, M	500			
7.5	B, C, J, K, M	250	7.5	B, C, J, K, M	150	7.5	B, C, J, K, M	500			
8.2	B, C, J, K, M	250	8.2	B, C, J, K, M	150	8.2	B, C, J, K, M	500			
9.1	B, C, J, K, M	250	9.1	B, C, J, K, M	150	9.1	B, C, J, K, M	500			
10	F, G, J, K, M	250	10	F, G, J, K, M	150	10	F, G, J, K, M	500			
11	F, G, J, K, M	250	11	F, G, J, K, M	150	11	F, G, J, K, M	500			
12	F, G, J, K, M	250	12	F, G, J, K, M	150	12	F, G, J, K, M	500			
13	F, G, J, K, M	250	13	F, G, J, K, M	150	13	F, G, J, K, M	500			
15	F, G, J, K, M	250	15	F, G, J, K, M	150	15	F, G, J, K, M	500			
16	F, G, J, K, M	250	16	F, G, J, K, M	150	16	F, G, J, K, M	500			
18	F, G, J, K, M	250	18	F, G, J, K, M	150	18	F, G, J, K, M	500			
20	F, G, J, K, M	250	20	F, G, J, K, M	150	20	F, G, J, K, M	500			
22	F, G, J, K, M	250	22	F, G, J, K, M	150	22	F, G, J, K, M	500			
24	F, G, J, K, M	250	24	F, G, J, K, M	150	24	F, G, J, K, M	500			
27	F, G, J, K, M	250	27	F, G, J, K, M	150	27	F, G, J, K, M	500			
30	F, G, J, K, M	250	30	F, G, J, K, M	150	30	F, G, J, K, M	500			
33	F, G, J, K, M	250	33	F, G, J, K, M	150	33	F, G, J, K, M	500			
36	F, G, J, K, M	50	36	F, G, J, K, M	150	36	F, G, J, K, M	500			
39	F, G, J, K, M	50	39	F, G, J, K, M	150	39	F, G, J, K, M	500			
43	F, G, J, K, M	50	43	F, G, J, K, M	150	43	F, G, J, K, M	500			
47	F, G, J, K, M	50	47	F, G, J, K, M	150	47	F, G, J, K, M	500			
51	F, G, J, K, M	50	51	F, G, J, K, M	150	51	F, G, J, K, M	500			
56	F, G, J, K, M	50	56	F, G, J, K, M	150	56	F, G, J, K, M	500			
62	F, G, J, K, M	50	62	F, G, J, K, M	150	62	F, G, J, K, M	500			
68	F, G, J, K, M	50	68	F, G, J, K, M	150	68	F, G, J, K, M	500			
75	F, G, J, K, M	50	75	F, G, J, K, M	150	75	F, G, J, K, M	500			
82	F, G, J, K, M	50	82	F, G, J, K, M	150	82	F, G, J, K, M	500			
91	F, G, J, K, M	50	91	F, G, J, K, M	150	91	F, G, J, K, M	500			
100	F, G, J, K, M	50	100	F, G, J, K, M	150						
120	F, G, J, K, M	50									



Microwave MLC's



AQ Series Available Capacitance/Size/WVDC/T.C.

TABLE II: TC: A (0±30PPM/°C)
CASE SIZE 06, 11, 12, 13 & 14

DIMENSIONS: inches (millimeters)





Case	Length	Width	Thickness	Band Width	Avail. Term.
06	.063±.006 (1.60±.152)	.032±.006 (.813±.152)	.035 Max. (.889)	.014±.006 (.357 ±.152)	J
11	.055±.015 (1.40±.381)	.055±.015 (1.40±.381)	.020/.057 (.508/1.45)	.010 +.010 -.005 (.254 +.254 -.127)	1 & 7
12	.055±.025 (1.40±.635)	.055±.015 (1.40±.381)	.020/.057 (.508/1.45)	.010 +.010 -.005 (.254 +.254 -.127)	J
13	.110±.020 (2.79±.508)	.110±.020 (2.79±.508)	.030/.102 (.762/2.59)	.015±.010 (.381±.254)	1 & 7
14	.110 +0.035 -0.020 (2.79 +.889 -.508)	.110±.020 (2.79±.508)	.030/.102 (.762/2.59)	.015±.010 (.381±.254)	J

Case: AQ06			Case: AQ11, AQ12						Case: AQ13, AQ14					
Cap. pF	Cap. Tol.	WVDC	Cap. pF	Cap. Tol.	WVDC	Cap. pF	Cap. Tol.	WVDC	Cap. pF	Cap. Tol.	WVDC	Cap. pF	Cap. Tol.	WVDC
0.1	B	250	0.1	B	150	24	F, G, J, K, M	150	0.1	B	500	51	F, G, J, K, M	500
0.2	B	250	0.2	B	150	27	F, G, J, K, M	150	0.2	B	500	56	F, G, J, K, M	500
0.3	B,C	250	0.3	B,C	150	30	F, G, J, K, M	150	0.3	B,C	500	62	F, G, J, K, M	500
0.4	B,C	250	0.4	B,C	150	33	F, G, J, K, M	150	0.4	B,C	500	68	F, G, J, K, M	500
0.5	B, C, D	250	0.5	B, C, D	150	36	F, G, J, K, M	150	0.5	B, C, D	500	75	F, G, J, K, M	500
0.6	B, C, D	250	0.6	B, C, D	150	39	F, G, J, K, M	150	0.6	B, C, D	500	82	F, G, J, K, M	500
0.7	B, C, D	250	0.7	B, C, D	150	43	F, G, J, K, M	150	0.7	B, C, D	500	91	F, G, J, K, M	500
0.8	B, C, D	250	0.8	B, C, D	150	47	F, G, J, K, M	150	0.8	B, C, D	500	100	F, G, J, K, M	500
0.9	B, C, D	250	0.9	B, C, D	150	51	F, G, J, K, M	150	0.9	B, C, D	500	110	F, G, J, K, M	300
1.0	B, C, D	250	1.0	B, C, D	150	56	F, G, J, K, M	150	1.0	B, C, D	500	120	F, G, J, K, M	300
1.1	B, C, D	250	1.1	B, C, D	150	62	F, G, J, K, M	150	1.1	B, C, D	500	130	F, G, J, K, M	300
1.2	B, C, D	250	1.2	B, C, D	150	68	F, G, J, K, M	150	1.2	B, C, D	500	150	F, G, J, K, M	300
1.3	B, C, D	250	1.3	B, C, D	150	75	F, G, J, K, M	150	1.3	B, C, D	500	160	F, G, J, K, M	300
1.4	B, C, D	250	1.4	B, C, D	150	82	F, G, J, K, M	150	1.4	B, C, D	500	180	F, G, J, K, M	300
1.5	B, C, D	250	1.5	B, C, D	150	91	F, G, J, K, M	150	1.5	B, C, D	500	200	F, G, J, K, M	300
1.6	B, C, D	250	1.6	B, C, D	150	100	F, G, J, K, M	150	1.6	B, C, D	500	220	F, G, J, K, M	200
1.7	B, C, D	250	1.7	B, C, D	150	110	F, G, J, K, M	50	1.7	B, C, D	500	240	F, G, J, K, M	200
1.8	B, C, D	250	1.8	B, C, D	150	120	F, G, J, K, M	50	1.8	B, C, D	500	270	F, G, J, K, M	200
1.9	B, C, D	250	1.9	B, C, D	150	130	F, G, J, K, M	50	1.9	B, C, D	500	300	F, G, J, K, M	200
2.0	B, C, D	250	2.0	B, C, D	150	150	F, G, J, K, M	50	2.0	B, C, D	500	330	F, G, J, K, M	200
2.2	B, C, D	250	2.2	B, C, D	150	160	F, G, J, K, M	50	2.2	B, C, D	500	360	F, G, J, K, M	200
2.4	B, C, D	250	2.4	B, C, D	150	180	F, G, J, K, M	50	2.4	B, C, D	500	390	F, G, J, K, M	200
2.7	B, C, D	250	2.7	B, C, D	150	200	F, G, J, K, M	50	2.7	B, C, D	500	430	F, G, J, K, M	200
3.0	B, C, D	250	3.0	B, C, D	150	220	F, G, J, K, M	50	3.0	B, C, D	500	470	F, G, J, K, M	200
3.3	B, C, D	250	3.3	B, C, D	150	240	F, G, J, K, M	50	3.3	B, C, D	500	510	F, G, J, K, M	150
3.6	B, C, D	250	3.6	B, C, D	150	270	F, G, J, K, M	50	3.6	B, C, D	500	560	F, G, J, K, M	150
3.9	B, C, D	250	3.9	B, C, D	150	300	F, G, J, K, M	50	3.9	B, C, D	500	620	F, G, J, K, M	150
4.3	B, C, D	250	4.3	B, C, D	150	330	F, G, J, K, M	50	4.3	B, C, D	500	680	F, G, J, K, M	150
4.7	B, C, D	250	4.7	B, C, D	150	360	F, G, J, K, M	50	4.7	B, C, D	500	750	F, G, J, K, M	150
5.1	B, C, D	250	5.1	B, C, D	150	390	F, G, J, K, M	50	5.1	B, C, D	500	820	F, G, J, K, M	150
5.6	B, C, D	250	5.6	B, C, D	150	430	F, G, J, K, M	50	5.6	B, C, D	500	910	F, G, J, K, M	150
6.2	B, C, D	250	6.2	B, C, D	150	470	F, G, J, K, M	50	6.2	B, C, D	500	1000	F, G, J, K, M	150
6.8	B, C, J, K, M	250	6.8	B, C, J, K, M	150	510	F, G, J, K, M	50	6.8	B, C, J, K, M	500	1100	F, G, J, K, M	50
7.5	B, C, J, K, M	250	7.5	B, C, J, K, M	150	560	F, G, J, K, M	50	7.5	B, C, J, K, M	500	1200	F, G, J, K, M	50
8.2	B, C, J, K, M	250	8.2	B, C, J, K, M	150	620	F, G, J, K, M	50	8.2	B, C, J, K, M	500	1300	F, G, J, K, M	50
9.1	B, C, J, K, M	250	9.1	B, C, J, K, M	150	680	F, G, J, K, M	50	9.1	B, C, J, K, M	500	1500	F, G, J, K, M	50
10	F, G, J, K, M	250	10	F, G, J, K, M	150	750	F, G, J, K, M	50	10	F, G, J, K, M	500	1600	F, G, J, K, M	50
11	F, G, J, K, M	250	11	F, G, J, K, M	150	820	F, G, J, K, M	50	11	F, G, J, K, M	500	1800	F, G, J, K, M	50
12	F, G, J, K, M	250	12	F, G, J, K, M	150	910	F, G, J, K, M	50	12	F, G, J, K, M	500	2000	F, G, J, K, M	50
13	F, G, J, K, M	250	13	F, G, J, K, M	150	1000	F, G, J, K, M	50	13	F, G, J, K, M	500	2200	F, G, J, K, M	50
15	F, G, J, K, M	250	15	F, G, J, K, M	150				15	F, G, J, K, M	500	2400	F, G, J, K, M	50
16	F, G, J, K, M	250	16	F, G, J, K, M	150				16	F, G, J, K, M	500	2700	F, G, J, K, M	50
18	F, G, J, K, M	250	18	F, G, J, K, M	150				18	F, G, J, K, M	500	3000	F, G, J, K, M	50
20	F, G, J, K, M	250	20	F, G, J, K, M	150				20	F, G, J, K, M	500	3300	F, G, J, K, M	50
22	F, G, J, K, M	250	22	F, G, J, K, M	150				22	F, G, J, K, M	500	3600	F, G, J, K, M	50
24	F, G, J, K, M	250							24	F, G, J, K, M	500	3900	F, G, J, K, M	50
27	F, G, J, K, M	250							27	F, G, J, K, M	500	4300	F, G, J, K, M	50
30	F, G, J, K, M	250							30	F, G, J, K, M	500	4700	F, G, J, K, M	50
33	F, G, J, K, M	250							33	F, G, J, K, M	500	5000	F, G, J, K, M	50
36	F, G, J, K, M	50							36	F, G, J, K, M	500	5100	F, G, J, K, M	50
39	F, G, J, K, M	50							39	F, G, J, K, M	500			
43	F, G, J, K, M	50							43	F, G, J, K, M	500			
47	F, G, J, K, M	50							47	F, G, J, K, M	500			
51	F, G, J, K, M	50												
56	F, G, J, K, M	50												
62	F, G, J, K, M	50												
68	F, G, J, K, M	50												
75	F, G, J, K, M	50												
82	F, G, J, K, M	50												
91	F, G, J, K, M	50												
100	F, G, J, K, M	50												
120	F, G, J, K, M	50												

TABLE III: TC: C (±15%) CASE SIZE 12 & 14


Case: AQ12									Case: AQ14								
Cap. pF	Cap. Tol.	WVDC	Cap. pF	Cap. Tol.	WVDC	Cap. pF	Cap. Tol.	WVDC	Cap. pF	Cap. Tol.	WVDC	Cap. pF	Cap. Tol.	WVDC	Cap. pF	Cap. Tol.	WVDC
1000	K, M, N	50	2200	K, M, N	50	5100	K, M, N	50	5000	K, M, N	50	15000	K, M, N	50	47000	K, M, N	50
1200	K, M, N	50	2700	K, M, N	50	5600	K, M, N	50	6800	K, M, N	50	18000	K, M, N	50	68000	K, M, N	50
1500	K, M, N	50	3300	K, M, N	50	6800	K, M, N	50	8200	K, M, N	50				82000	K, M, N	50
1800	K, M, N	50	3900	K, M, N	50	8200	K, M, N	50	10000	K, M, N	50	27000	K, M, N	50	100000	K, M, N	50
2000	K, M, N	50	4700	K, M, N	50	10000	K, M, N	50	12000	K, M, N	50	33000	K, M, N	50			
												39000	K, M, N	50			






Microwave MLC's


Performance Curves




AVX CORPORATION
 1 Picofarad -.-.- 10 Picofarad - - - 47 Picofarad — 330 Picofarad







AVX CORPORATION
 1 Picofarad - - - 15 Picofarad — 100 Picofarad









AVX CORPORATION
 250 MHz - - - 500 MHz — 1000 MHz



AVX CORPORATION
 — 250 MHz - - - 500 MHz 1000 MHz







Microwave MLC's

Automatic Insertion Packaging

TAPE & REEL: All tape and reel specifications are in compliance with EIA RS481 (equivalent to IEC 286 part 3).


Sizes AQ11/12 through 13/14, CDR11/12 through 13/14.

- 8mm carrier
- 7" reel: ≤ 0.040 " thickness = 2000 pcs
 ≤ 0.075 " thickness = 2000 pcs
- 13" reel: ≤ 0.075 " thickness = 10,000 pcs

"U" Series - 0603/0805/1210 Size Chips

- 8mm carrier
- 7" reel: 0603 & 0805 ≤ 0.40 " thickness = 4000 pcs
0805 . 0.040" thickness & 1210= 2000 pcs
- 13" reel: ≤ 0.075 " thickness = 10,000 pcs

REEL DIMENSIONS: millimeters (inches)



Tape Size ⁽¹⁾	A Max.	B* Min.	C	D* Min.	N Min.	W ₁	W ₂ Max.	W ₃
8mm	330 (12.992)	1.5 (.059)	13.0±0.20 (.512±.008)	20.2 (.795)	50 (1.969)	8.4 ^{+1.0} _{-0.0} (.331 ^{+0.060} _{-0.0})	14.4 (.567)	7.9 Min. (.311) 10.9 Max. (.429)
12mm						12.4 ^{+2.0} _{-0.0} (.488 ^{+0.075} _{-0.0})	18.4 (.724)	11.9 Min. (.469) 15.4 Max. (.607)


Metric dimensions will govern.
English measurements rounded and for reference only.
(1) For tape sizes 16mm and 24mm (used with chip size 3640) consult EIA RS-481 latest revision.

EMBOSSED CARRIER CONFIGURATION

8 & 12 MM TAPE ONLY

CONSTANT DIMENSIONS

Tape Size	D ₀	E	P ₀	P ₂	T Max.	T ₁	G ₁	G ₂
8mm and 12mm	8.4 ^{+0.10} _{-0.0} (.059 ^{+0.004} _{-0.0})	1.75 ± 0.10 (.069 ± .004)	4.0 ± 0.10 (.157 ± .004)	2.0 ± 0.05 (.079 ± .002)	0.600 (.024)	0.10 (.004) Max.	0.75 (.030) Min. See Note 3	0.75 (.030) Min. See Note 4



VARIABLE DIMENSIONS

Tape Size	B ₁ Max. See Note 6	D ₁ Min. See Note 5	F	P ₁	R Min. See Note 2	T ₂	W	A ₀ B ₀ K ₀
8mm	4.55 (.179)	1.0 (.039)	3.5 ± 0.05 (.138 ± .002)	4.0 ± 0.10 (.157 ± .004)	25 (.984)	2.5 Max (.098)	8.0 ^{+0.3} _{-0.1} (.315 ^{+0.012} _{-0.004})	See Note 1
12mm	8.2 (.323)	1.5 (.059)	5.5 ± 0.05 (.217 ± .002)	4.0 ± 0.10 (.157 ± .004)	30 (1.181)	6.5 Max (.256)	12.0 ± .30 (.472 ± .012)	See Note 1

NOTES:

- A₀, B₀, and K₀ are determined by the max. dimensions to the ends of the terminals extending from the component body and/or the body dimensions of the component. The clearance between the end of the terminals or body of the component to the sides and depth of the cavity (A₀, B₀, and K₀) must be within 0.05 mm (.002) min. and 0.50 mm (.020) max. The clearance allowed must also prevent rotation of the component within the cavity of not more than 20 degrees (see sketches C & D).
- Tape with components shall pass around radius "R" without damage. The minimum trailer length (Note 2 Fig. 3) may require additional length to provide R min. for 12mm embossed tape for reels with hub diameters approaching N min. (Table 4).
- G₁ dimension is the flat area from the edge of the sprocket hole to either the outward deformation of the carrier tape between the embossed cavities or to the edge of the cavity whichever is less.
- G₂ dimension is the flat area from the edge of the carrier tape opposite the sprocket holes to either the outward deformation of the carrier tape between the embossed cavity or to the edge of the cavity whichever is less.
- The embossment hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of embossment location and hole location shall be applied independent of each other.
- B₁ dimension is a reference dimension for tape feeder clearance only.

