




Connectors > PCB Connectors > Card Edge Connectors > PCI & PCI Express Connectors



Connector System: **Board-to-Board**

Number of Positions: **184**

Centerline (Pitch): **1.27 mm [.05 in]**

Contact Mating Area Plating Material Thickness: **[30 µin]**

PCB Mount Orientation: **Vertical**

Features

Product Type Features

| | |
|-----------------------------------|-----------------------|
| Connector & Contact Terminates To | Printed Circuit Board |
| Connector System | Board-to-Board |

Configuration Features

| | |
|--|----------|
| Number of PCB Mount Retention Features | 2 |
| Number of Positions | 184 |
| PCB Mount Orientation | Vertical |
| Ejector | Without |

Electrical Characteristics

| | |
|-------------------|---------|
| Operating Voltage | 203 VAC |
|-------------------|---------|

Body Features

| | |
|--|----------|
| PCB Retention Feature Material | Brass |
| PCB Retention Feature Plating Material | Tin |
| Product Weight | 15.903 g |
| Primary Product Color | Natural |

Contact Features

| | |
|--------------------------------------|-----------------|
| Contact Current Rating (Max) | 1.1 A |
| Contact Underplating Material | Nickel |
| Contact Mating Area Plating Material | Gold (Au) |
| Contact Base Material | Phosphor Bronze |



| | |
|---|--------|
| PCB Contact Termination Area Plating Material | Tin |
| | 30 µin |

Termination Features

| | |
|---------------------------|---------------|
| Termination Method to PCB | Surface Mount |
|---------------------------|---------------|

Mechanical Attachment

| | |
|--------------------------|----------------|
| Connector Mounting Type | Board Mount |
| PCB Mount Retention Type | Hold-Down Post |

Housing Features

| | |
|--------------------|--------------------------------|
| Housing Material | High Temperature Thermoplastic |
| Centerline (Pitch) | 1.27 mm [.05 in] |

Dimensions

| | |
|--------------------------|-------------------|
| PCB Thickness (Accepted) | .62 mm [.024 in] |
| Connector Length | 5.04 mm [.198 in] |
| Connector Height | 15.49 mm [.61 in] |
| Connector Width | .35 mm [.014 in] |

Usage Conditions

| | |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 85 °C [-67 – 185 °F] |
|-----------------------------|----------------------------|

Operation/Application

| | |
|---------------------|--------|
| Circuit Application | Signal |
|---------------------|--------|

Industry Standards

| | |
|----------|-----|
| Bus Type | PCI |
|----------|-----|

Packaging Features

| | |
|--------------------|--------------|
| Packaging Method | Box & Carton |
| Packaging Quantity | 32 |

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Not Yet Reviewed |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Not reviewed for China RoHS compliance |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2025 (247) |



Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

| | |
|---------------------------|--|
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Reflow solder capable to 245°C |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1761842-1
CONNECTOR ASSY, 60 DUAL POSITI




TE Part # 5-2337939-4
PCIE GEN4 CON,SMT,164POS,30u", MYLAR,HT



TE Part # 1734774-1
PCI EXP 3.1L 36 POS WHT G/F


Customers Also Bought



TE Part #5747841-4
15 MSFL PLUG RA 318 (IN,FM,BL)



TE Part #5413879-1
JACK ASSY,RTANG,BNC



TE Part #2-520194-2
ULTRAFAST 187 ASSY REC 22-18 TPBR LP



TE Part #3-2176331-1
CRGP 2512 3K3 1%



TE Part #5-2176094-2
RP 2A 0.25W 412K 0.1% 25PPM 1K RL

TE Part #4-1393779-4
V23101D1106B201(stronger packaging)

TE Part #NB15312001
CRN-1/8-0-STK

TE Part #3-1761608-0
IDC LOW PRO HDR 30P VERT SHT L

TE Part #5-1761184-1
4 SDL FLAT PLUG ASSY

TE Part #5499374-2
A/L UNIV HDR 14P VERT SHT LAT

Documents

Product Drawings

CONNECTOR ASSEMBLY, DUAL POSIT

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_5145113-1_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_5145113-1_O.3d_igs.zip

English

Customer View Model

ENG_CVM_5145113-1_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English