

Product data sheet

Specifications



Repacked, add-on residual current device, Acti9 Vigi iC60, 4P, 63A, AC type, instantaneous, 30mA, 400...415VAC

A9V11463W



This repacked option saves 2.097 over the standard condition

Main

Range	Acti9
Product name	Acti9 Vigi iC60
Product or component type	Add-on residual current device
Device short name	Vigi iC60
Poles description	4P
[In] rated current	63 A
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth leakage protection type	Type AC
Network type	AC
Network frequency	50/60 Hz
[Ue] rated operational voltage	400...415 V AC 50/60 Hz conforming to EN/IEC 61009-1 400...415 V AC 50/60 Hz conforming to EN/IEC 61009-2-1
Standards	EN/IEC 61009-1 EN/IEC 61009-2-1
9 mm pitches	7

Complementary

Device location in system	Outgoer
Residual current tripping technology	Voltage independent
[Ui] rated insulation voltage	500 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-2
Range compatibility	Acti9 iC60 Acti9 Reflex iC60
Product compatibility	Single terminal
Local signalling	Trip indicator
Mounting mode	Clip-on
Mounting support	DIN rail
Electrical connection to mcb	By screws
Comb busbar and distribution block compatibility	Bottom: YES
Height	91 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	135 mm
Depth	73.5 mm
Product weight	0.245 kg
Connections - terminals	Tunnel type terminal downside for 1 cable(s) 1...35 mm² rigid without cable end Tunnel type terminal downside for 1 cable(s) 1...25 mm² flexible without cable end Tunnel type terminal downside for 1 cable(s) 1...25 mm² flexible with cable end
Wire stripping length	14 mm for bottom connection
Tightening torque	3.5 N.m bottom

Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3 conforming to IEC 60947-2
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to IEC 61009-1
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...85 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	12.0 cm
Package 1 Length	14.6 cm
Package 1 Weight	279.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	15
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.78 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Lower carbon footprint

2 kg CO2 eq.

Use Better



Materials and Substances

Packaging made with recycled cardboard

No

Packaging without single use plastic

No

SCIP Number

A7b24ae6-2312-4e67-b7c9-56fce3e8c723

EU RoHS Directive

[Compliant By Exemption](#)

REACH Regulation

[Reference contains Substances of Very High Concern above the threshold](#)

Use Longer



Lifetime extension

Repair

No

Use Again



Repack and remanufacture

WEEE Label



The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins