SURFACE MOUNT LED WHITE, 1206 IL PACKAGE




SM1206NUWC-IL

- Industry Standard 1206 Package
- RoHS Compliant
- Diffused Inner Lens
- High Luminous Intensity
- Narrow Viewing Angle
- Ideal for Status Indication, Display, and Backlighting

Bivar Surface Mount 1206 Inner Lens package LED may be used in nearly any indication application. The diffused inner lens provides a narrow viewing angle and high luminous intensity making it suitable for small scale applications such as display, backlighting, and general indication. Low power consumption and excellent long life reliability are ideal for battery powered equipment. Wide variety of wavelength and intensity combinations are available to meet any illumination need. The SM1206-IL LED is packaged in standard tape and reels for pick and place assemblies.

| Part Number | Material | Emitted Color | Chromaticity Coordinates (±.05) | Lens Appearance | Luminous Intensity (mcd) TYP. | Viewing Angle | |
|---------------|----------|---------------|---------------------------------------|--------------------|-------------------------------------|---------------|--|
| SM1206NUWC-IL | InGaN | WHITE | X=.30, Y=.29 | Diffused | 750 | 30° | |

Outline Dimensions



Outline Drawings Notes:

1. All dimensions are in inches [millimeters].

2. Standard tolerance: ±0.010" unless otherwise noted.



Bivar reserves the right to make changes at any time without notice.



Absolute Maximum Ratings

 $T_A = 25^{\circ}C$ unless otherwise noted

| Power Dissipation | 100 mW |
|--|-------------|
| Forward Current (DC) | 25 mA |
| Peak Forward Current ¹ | 100 mA |
| Reverse Voltage | 5 V |
| Operating Temperature Range | -30 ~ +80°C |
| Storage Temperature Range | -40 ~ +85°C |
| Lead Soldering Temperature (3 mm from the base of the epoxy bulb) ² | 260°C |
| | |

Notes: 1. 10% Duty Cycle, Pulse Width \leq 0.1 msec. 2. Solder time less than 5 seconds at temperature extreme.

Electrical / Optical Characteristics

 $T_A = 25^{\circ}C \& I_F = 20 \text{ mA}$ unless otherwise noted


| Part Number | Forward Voltage (V) ¹ | | Recommend Forward Current (mA) | | Reverse Current (µA) | Dominant Wavelength (nm) ² | | Luminous Intensity Iv (mcd) | | | Viewing Angle 2 O ¹ / ₂ (deg) | | | |
|---------------|-------------------------------------|-----|--------------------------------------|-----|----------------------------|--|-----|--------------------------------|-----|-----|--|-----|-----|-----|
| | MIN | ΤΥΡ | MAX | MIN | ΤΥΡ | MAX | MAX | MIN | TYP | MAX | MIN | ΤΥΡ | MAX | ТҮР |
| SM1206NUWC-IL | / | 3.1 | 4.2 | / | 20 | / | 10 | / | / | / | 450 | 750 | / | 30 |

Notes: 1. Tolerance of forward voltage : ±0.05V. 2. Tolerance of dominant wavelength : ±5.0nm.

Bivar reserves the right to make changes at any time without notice.




Typical Electrical / Optical Characteristics T_A = 25°C unless otherwise noted




SURFACE MOUNT LED WHITE, 1206 IL PACKAGE



Recommended Soldering Conditions



Tape and Reel Dimensions Note: 3000 pcs/Reel




All dimensions are in inches [millimeters].
Standard tolerance: ±0.010" unless otherwise noted.

Bivar reserves the right to make changes at any time without notice.

SURFACE MOUNT LED WHITE, 1206 IL PACKAGE






Outline Drawings Notes:

1. All dimensions are in inches [millimeters]. 2. Standard tolerance unless otherwise noted: X.XXX ± 0.010"

X.X ± 0.1'

Packaging and Labeling Plan Note: 1 Reel / Bag



| Part No. | XXXX-XXX-XXX |
|-----------|--------------|
| Prod. No. | XXXX-XXX-XXX |
| PO No. | XXXX |
| Lot No. | XXXXXXXXX |
| Q'ty: | X.XXX PCS |
| Q.C. | XXX BIN |
| Date: | 2008.XX.XX |

Internal Quality Control

| Bivar. Inc. | MSL4 | | | | | | |
|---------------------------------|-------------------|--|--|--|--|--|--|
| 4 Thomas, Irvine, CA 92618-2593 | | | | | | | |
| LOT: XXX.XXXXX.X | ~ | | | | | | |
| | | | | | | | |
| Part: XXXX-XXX-XXX | | | | | | | |
| Quantity: X.XXX | RoHS Compliant | | | | | | |

Bivar Standard Packaging Label