




TE Internal #: 2441519-1

N Type Connector, Plug, 50 ohm, Screw, 0 – 6 GHz, 1 Position, -65 – 165 °C [-85 – 329 °F], Straight, Brass, Plated, Nickel, Mechanical, Bag & Box

[View on TE.com >](#)

Connectors > RF Connectors > Coax Connectors



RF Interface: **N Type**

RF Connector Style: **Plug**

Impedance: **50 Ω**

RF Connector Coupling Mechanism: **Screw**

Operating Frequency: **0 – 6 GHz**

Features

Product Type Features

RF Interface	N Type
RF Connector Style	Plug
Sealable	No

Configuration Features

Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Cable Connector Orientation	Straight
Body Material	Brass
Body Material Finish	Plated
Body Plating Material	Nickel

Mechanical Attachment



RF Connector Coupling Mechanism	Screw
RF Contact Captivation Method	Mechanical
Detent	Without

Usage Conditions

Operating Temperature Range	-65 – 165 °C[-85 – 329 °F]
-----------------------------	----------------------------

Operation/Application

Operating Frequency	0 – 6 GHz
---------------------	-----------

Packaging Features

Packaging Method	Bag & Box
------------------	-----------

Other

Dielectric Material	PTFE
---------------------	------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (4.75% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for



substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




TE Part # 1-1337417-0  
N BHSkt 50Ohm Silver Pltd




TE Part # 2441543-1  
N F TO QUICK LOCK N M ADAPTOR BMRF


Customers Also Bought




TE Part #CAT-P592-R472A  
PIDG Ring Tongue Terminals




TE Part #193673-2  
SKT ASSY.,CRIMP, 4MM, 10AWG




TE Part #749806-8  
KIT, HDP-20,RCPT,SIZE 2, 15 PO



TE Part #1-794610-1  
MICRO MNL RPT CNT,LS PC 15AU L



TE Part #1-794612-0  
PIN CONT 20-24 TIN PLATE L/P



TE Part #1658681-1  
HDP-22,RCPT,SIZE 1,15 POSN

Documents

Product Drawings  
N MALE TERMINATOR.STR,6G RFT

English

CAD Files  
3D PDF  
3D  
Customer View Model  
ENG\_CVM\_CVM\_2441519-1\_1.2d\_dxf.zip

English



Customer View Model

[ENG\\_CVM\\_CVM\\_2441519-1\\_1.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2441519-1\\_1.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[dnd-flyer-rf-connector-ca-tm-en](#)

English

[dnd-fly-rf-connector-catm-cn-0224](#)

Product Specifications

[Product Specification](#)

English