


ESH, Aluminum Electrolytic, 220 μ F, 20%, 25 VDC, -40/+105°C, Lead Spacing = 3.5mm**Dimensions**

D	8mm +/-0.5mm
L	11mm +1.5mm
S	3.5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	20mm MIN
F	0.6mm NOM

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	6000

General Information

Supplier:	KEMET
Series:	ESH
Dielectric:	Aluminum Electrolytic
Description:	High CV Single Ended Aluminum Electrolytic
Features:	High CV
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No

Specifications

Capacitance:	220 μ F
Capacitance Tolerance:	20%
Voltage DC:	25 VDC, 32 VDC (Surge)
Temperature Range:	-40/+105°C
Rated Temperature:	105°C
Life:	2000 Hrs
Dissipation Factor:	16.00% 120Hz 25C
Ripple Current:	250 mAmps (120Hz 105C)
Leakage Current:	55 μ A (2min 20°C)
Impedance Ratio at -25C:	2
Impedance Ratio at -40C:	3