

FEATURES

- 16"Adjustable Probe
- Replaceable Sensor
- TRI Mode Detection

RS PRO Combustible Handheld Gas Detector, For Leak Detection

RS Stock No.: 144-5342



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Introducing the RS PRO Handheld Gas Detector which is able to locate and detect combustible and explosive gas leaks like methane, propane, butane, ammonia, carbon dioxide and many more. It can detect concentrations as low as 1ppm and up to 1000ppm, meaning it can operate in the most difficult environments with minimal interference. This effective and easy to use gas detection unit from RS PRO is ideal for ensuring proper installation of gas lines, maintenance and repair tasks and is simple enough to use to quickly pinpoint combustible gas leaks across a variety of different applications.

General Specifications

Gas Detected	Combustible
Response Time	2s
Meter Type	Handheld
Display Type	LED
Audible Alarm	Yes
Visual Alarm	Yes
Power Source	Battery
Battery Type	Li-ion polymer
Sensitivity	<50 ppm(methane)
ATEX Approval	No
Application	Boiler Plant Room, Automotive Industries, Welding, Power Plants, Refrigeration Plants, Textile Industry



