



Part Number : [1501700003](#)
Product Description : Ditto Hermaphroditic Crimp Housing, Positive Lock, 3 Circuit
Series Number : 150170
Status : Not Recommended For New Design
Product Category : Connector Housings



Documents & Resources

Drawings


- [1501700003_sd.pdf](#)
- [PK-150170-0000-000.pdf](#)
- [1501700003_stp.zip](#)

Specifications

- [1501700000-AS-000.pdf](#)
- [TS-150170-0000-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Connector Housings
Series	150170
Description	Ditto Hermaphroditic Crimp Housing, Positive Lock, 3 Circuit
Application	Power, Wire-to-Wire
Product Name	Ditto
UPC	889056215671

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	3
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Hermaphroditic
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.948/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm

Temperature Range - Operating	-40° to +105°C, -40° to +80°C, See Product Specification
-------------------------------	--

Mates With / Use With

Mates with Part(s)

Description	Part Number
Ditto Hermaphroditic Crimp Housings	<u>150170</u>

Use with Part(s)

Description	Part Number
Ditto Hermaphroditic Crimp Terminals	<u>150200</u>
Ditto Terminal Position Assurance (TPA) Retainers	<u>150212</u>