


# MSC750SMA170B4 Silicon Carbide N-Channel Power MOSFET

# **Product Overview**

The silicon carbide (SiC) power MOSFET product line from Microsemi increases the performance over silicon MOSFET and silicon IGBT solutions while lowering the total cost of ownership for high-voltage applications. The MSC750SMA170B4 device is a 1700 V, 750 m $\Omega$  SiC MOSFET in a TO-247 package with a source sense.



### Features

The following are key features of the MSC750SMA170B4 device:

- Low capacitances and low gate charge
- Fast switching speed due to low internal gate resistance (ESR)
- Stable operation at high junction temperature, T<sub>J(max)</sub> = 175 °C
- Fast and reliable body diode
- Superior avalanche ruggedness
- RoHS compliant

### Benefits

The following are benefits of the MSC750SMA170B4 device:

- High efficiency to enable lighter, more compact system
- Simple to drive and easy to parallel
- Improved thermal capabilities and lower switching losses
- Eliminates the need for external freewheeling diode
- Lower system cost of ownership

### Applications

The MSC750SMA170B4 device is designed for the following applications:

- PV inverter, converter, and industrial motor drives
- Smart grid transmission and distribution
- Induction heating and welding
- H/EV powertrain and EV charger
- Power supply and distribution



# **Device Specifications**

This section shows the specifications of the MSC750SMA170B4 device.

### **Absolute Maximum Ratings**

The following table shows the absolute maximum ratings of the MSC750SMA170B4 device.

#### Table 1 • Absolute Maximum Ratings

Symbol	Characteristic	Ratings	Unit
V <sub>DSS</sub>	Drain source voltage	1700	V
I <sub>D</sub>	Continuous drain current at $T_C = 25 \ ^\circ C$	7	А
	Continuous drain current at T <sub>C</sub> = 100 °C	5	
I <sub>DM</sub>	Pulsed drain current <sup>1</sup>	12	
V <sub>GS</sub>	Gate-source voltage	23 to -10	V
P <sub>D</sub>	Total power dissipation at $T_{C} = 25 \text{ °C}$	68	W
	Linear derating factor	0.46	w/℃

#### Note:

1. Repetitive rating: pulse width and case temperature limited by maximum junction temperature.

The following table shows the thermal and mechanical characteristics of the MSC750SMA170B4 device. **Table 2 • Thermal and Mechanical Characteristics** 

Symbol	Characteristic	Min	Тур	Max	Unit
R <sub>θJC</sub>	Junction-to-case thermal resistance		1.46	2.19	°C/W
Тյ	Operating junction temperature			175	°C
T <sub>STG</sub>	Storage temperature	-55		150	
TL	Soldering temperature for 10 seconds (1.6 mm from case)			260	
	Mounting torque, 6-32 or M3 screw			10	lbf-in
				1.1	N-m
Wt	Package weight		0.22		OZ
			6.2		g



## **Electrical Performance**

The following table shows the static characteristics of the MSC750SMA170B4 device. T<sub>J</sub> = 25  $^{\circ}$ C unless otherwise specified.

Table 3 • Static Characteristics

Symbol	Characteristic	Test Conditions	Min	Тур	Max	Unit
V <sub>(BR) DSS</sub>	Drain-source breakdown voltage	$V_{GS}$ = 0 V, I <sub>D</sub> = 100 $\mu$ A	1700			V
R <sub>DS(on)</sub>	Drain-source on resistance <sup>1</sup>	V <sub>GS</sub> = 20 V, I <sub>D</sub> = 2.5 A		750	940	mΩ
V <sub>GS(th)</sub>	Gate-source threshold voltage	$V_{GS} = V_{DS}$ , $I_D = 100 \ \mu A$	1.8	3.25		V
$\Delta V_{GS(th)} / \Delta T_J$	Threshold voltage coefficient	$V_{GS} = V_{DS}$ , $I_D = 100 \ \mu A$		-5.7		mV/°C
I <sub>DSS</sub>	Zero gate voltage drain current	V <sub>DS</sub> = 1700 V, V <sub>GS</sub> = 0 V			100	μΑ
		V <sub>DS</sub> = 1700 V, V <sub>GS</sub> = 0 V T <sub>J</sub> = 125 °C			500	
I <sub>GSS</sub>	Gate-source leakage current	V <sub>GS</sub> = 20 V/-10 V			±100	nA

### Note:

**1.** Pulse test: pulse width < 380 μs, duty cycle < 2%.

The following table shows the dynamic characteristics of the MSC750SMA170B4 device. T<sub>J</sub> = 25  $^{\circ}$ C unless otherwise specified.

#### **Table 4 • Dynamic Characteristics**

Symbol	Characteristic	Test Conditions	Min	Тур	Max	Unit
C <sub>iss</sub>	Input capacitance	V <sub>GS</sub> = 0 V, V <sub>DD</sub> = 1360 V V <sub>AC</sub> = 25 mV, f = 1 MHz		184		pF
C <sub>rss</sub>	Reverse transfer capacitance	· ( , )		2		
C <sub>oss</sub>	Output capacitance			14		
Qg	Total gate charge	V <sub>GS</sub> = -5 V/20 V, V <sub>DD</sub> = 1200 V I <sub>D</sub> = 2.5 A		11		nC
Q <sub>gs</sub>	Gate-source charge			2.9		
Q <sub>gd</sub>	Gate-drain charge			2.1		
t <sub>d(on)</sub>	Turn-on delay time	$V_{DD}$ = 1200 V, $V_{GS}$ = -5 V/20 V I <sub>D</sub> = 5 A, R <sub>G(ext)</sub> = 8 Ω,		13		ns
t <sub>f</sub>	Voltage fall time	Freewheeling diode = MSC750SMA170B4 (V <sub>GS</sub> = -5 V)		12		
t <sub>d(off)</sub>	Turn-off delay time	(VGS - 5 V)		7		



Symbol	Characteristic	Test Conditions	Min	Тур	Max	Unit
t <sub>r</sub>	Voltage rise time			8		
Eon	Turn-on switching energy			107		μ
E <sub>off</sub>	Turn-off switching energy			17		_
t <sub>d(on)</sub>	Turn-on delay time	$V_{DD} = 1200 V, V_{GS} = -5 V/20 V$		13		ns
t <sub>f</sub>	Voltage fall time	$I_D = 5 A, R_{G(ext)} = 8 \Omega, T_J = 150 °C$ Freewheeling diode =		12		_
t <sub>d(off)</sub>	Turn-off delay time	MSC750SMA170B4 (V <sub>GS</sub> = –5 V)		7		_
t <sub>r</sub>	Voltage rise time			8		
E <sub>on</sub>	Turn-on switching energy			185		μ
E <sub>off</sub>	Turn-off switching energy			20		_
ESR	Equivalent series resistance	f = 1 MHz, 25 mV, drain short		2.89		Ω
SCWT	Short circuit withstand time	$V_{DS}$ = 1200 V, $V_{GS}$ = 20 V		2.5		μs
E <sub>AS</sub>	Avalanche energy, single pulse	$V_{DS}$ = 150 V, $V_{GS}$ = 20 V, $I_{D}$ = 2.5 A		360		mJ



The following table shows the body diode characteristics of the MSC750SMA170B4 device.  $T_J = 25$  °C unless otherwise specified.

Table 5 • Body Diode Characteristics

Symbol	Characteristic	Test Conditions	Min	Тур	Max	Unit
V <sub>SD</sub>	Diode forward voltage	$I_{SD} = 2.5 \text{ A}, \text{ V}_{GS} = 0 \text{ V}$		3.8		V
		$I_{SD} = 2.5 \text{ A}, \text{ V}_{GS} = -5 \text{ V}$		3.9		V
t <sub>rr</sub>	Reverse recovery time	$I_{SD} = 5 \text{ A}, V_{GS} = -5 \text{ V},$ $V_{DD} = 1200 \text{ V}, \text{ dI/dt} = -2000 \text{ A/}\mu\text{s}$		18		ns
Q <sub>rr</sub>	Reverse recovery charge	Drive Rg = 8 $\Omega$		120		nC
I <sub>RRM</sub>	Reverse recovery current			3.0		A

## **Typical Performance Curves**

This section shows the typical performance curves of the MSC750SMA170B4 device.






Figure 1 • Drain Current vs. V<sub>DS</sub>



















Figure 5 • RDS(on) vs. Junction Temperature





Figure 6 • Gate Charge Characteristics




-75 °C

25 °C













Figure 10 •  $I_D$  vs.  $V_{DS}$  3<sup>rd</sup> Quadrant Conduction










Figure 12 • Switching Energy vs. V<sub>DS</sub> & I<sub>D</sub>




Figure 13 • Switching Energy vs. Rg





Figure 14 • Switching Energy vs. Temperature










Figure 17 • Maximum Transient Thermal Impedance




# **Package Specification**

This section shows the package specification of the MSC750SMA170B4 device.

## Package Outline Drawing

The following figure illustrates the TO-247 4-lead package outline of the MSC750SMA170B4 device.



#### Figure 18 • Package Outline Drawing

The following table shows the TO-247 4-lead dimensions and should be used in conjunction with the package outline drawing.

#### Table 6 • TO-247-4L Dimensions

Symbol	Min (mm)	Max (mm)	Min (in.)	Max (in.)
А	4.90	5.17	0.193	0.204
В	1.85	2.11	0.073	0.083
с	2.25	2.51	0.089	0.099
D	0.55	0.68	0.022	0.027
E	5.49	5.74	0.216	0.226



Symbol	Min (mm)	Max (mm)	Min (in.)	Max (in.)			
F	3.56	3.66	0.140	0.144			
G	6.15 BSC		0.242 BSC				
Н	20.83	21.08	0.820	0.830			
I	19.81	20.32	0.780	0.800			
J	1.07	1.33	0.042	0.052			
К	15.77	16.03	0.621	0.631			
L	13.89	14.15	0.547	0.557			
М	16.25	16.85	0.640	0.663			
N	2.00	2.75	0.079	0.108			
0	7.10	7.50	0.280	0.295			
Р	2.87 BSC		0.113 BSC				
Q	5.08 BSC		0.200 BSC				
R	2.54 BSC		0.100 BSC				
Terminal 1	Drain		·				
Terminal 2	Source	Source					
Terminal 3	Source sense						
Terminal 4	Gate						
Terminal 5	Drain						





Microsemi 2355 W. Chandler Blvd. Chandler, AZ 85224 USA

Within the USA: +1 (480) 792-7200 Fax: +1 (480) 792-7277

www.microsemi.com  $^{\textcircled{C}}$  2020 Microsemi and its corporate affiliates. All rights reserved. Microsemi and the Microsemi logo are trademarks of Microsemi Corporation and its corporate affiliates. All other trademarks and service marks are the property of their respective owners. Microsemi's product warranty is set forth in Microsemi's Sales Order Terms and Conditions. Information contained in this publication is provided for the sole purpose of designing with and using Microsemi products. Information regarding device applications and the like is provided only for your convenience and may be superseded by updates. Buyer shall not rely on any data and performance specifications or parameters provided by Microsemi. It is your responsibility to ensure that your application meets with your specifications. THIS INFORMATION IS PROVIDED "AS IS." MICROSEMI MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, NON-INFRINGEMENT, MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. IN NO EVENT WILL MICROSEMI BE LIABLE FOR ANY INDIRECT, SPECIAL, PUNITIVE, INCIDENTAL OR CONSEQUENTIAL LOSS, DAMAGE, COST OR EXPENSE WHATSOEVER RELATED TO THIS INFORMATION OR ITS USE, HOWEVER CAUSED, EVEN IF MICROSEMI HAS BEEN ADVISED OF THE POSSIBILITY OR THE DAMAGES ARE FORESEEABLE. TO THE FULLEST EXTENT ALLOWED BY LAW, MICROSEMI'S TOTAL LIABILITY ON ALL CLAIMS IN RELATED TO THIS INFORMATION OR ITS USE WILL NOT EXCEED THE AMOUNT OF FEES, IF ANY, YOU PAID DIRECTLY TO MICROSEMI FOR THIS INFORMATION. Use of Microsemi devices in life support, mission-critical equipment or applications, and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend and indemnify Microsemi from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microsemi intellectual property rights unless otherwise stated.

Microsemi Corporation, a subsidiary of Microchip Technology Inc. (Nasdaq: MCHP), and its corporate affiliates are leading providers of smart, connected and secure embedded control solutions. Their easy-to-use development tools and comprehensive product portfolio enable customers to create optimal designs which reduce risk while lowering total system cost and time to market. These solutions serve more than 120,000 customers across the industrial, automotive, consumer, aerospace and defense, communications and computing markets. Headquartered in Chandler, Arizona, the company offers outstanding technical support along with dependable delivery and quality. Learn more at **www.microsemi.com**.

050-7774 | July 2020 | Released