

Eaton 103032

Eaton Moeller series NZM - Molded Case Circuit Breaker. Circuit-breaker, 3p, 26A, N1-S26-CNA

UL/CSA

Product specifications

Type

Circuit breaker

Special features

Rated current = rated
uninterrupted current: 26 A
This circuit-breaker is only
allowed to be used for
UL/CSA applications.
Motor protection in
conjunction with contactor
and overload relay
With short-circuit release
Without overload release Ir

Application

Branch circuits, feeder circuits

Amperage Rating

26 A

Voltage rating

690 V - 690 V

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

Resources

Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Characteristic curve

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-058.eps](#)

[eaton-circuit-breaker-let-through-current-nzm-mccb-characteristic-curve-002.eps](#)

[eaton-circuit-breaker-nzm-mccb-characteristic-curve.eps](#)

Declarations of conformity

[DA-DC-03_N1](#)

Drawings

[eaton-circuit-breaker-switch-nzm-mccb-dimensions-014.eps](#)

[eaton-circuit-breaker-nzm-mccb-dimensions-017.eps](#)

[eaton-circuit-breaker-switch-nzm-mccb-3d-drawing-006.eps](#)

Installation instructions

[eaton-circuit-breaker-switch-disconnector-nzmb-il01203004z.pdf](#)

Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

mCAD model

[DA-CS-nzm1_3p](#)

[DA-CD-nzm1_3p](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Pollution degree

3

Mounting Method

Built-in device fixed built-in technique

Fixed

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

Equipment heat dissipation, current-dependent

2.13 W

Isolation

300 V AC (between the auxiliary contacts)

500 V AC (between auxiliary contacts and main contacts)

Ambient operating temperature - max

70 °C

Ambient operating temperature - min

-25 °C

Ambient storage temperature - max

70 °C

Ambient storage temperature - min

-40 °C

Protection against direct contact

Finger and back-of-hand proof to VDE 0106 part 100

Rated insulation voltage (Ui)

690 V

Rated operating power at AC-3, 230 V

5.5 kW

Rated operating power at AC-3, 400 V

11 kW

Switch off technique

Magnetic

Degree of protection

IP20 (basic degree of protection, in the operating controls area)

IP20

Direction of incoming supply

As required

Electrical connection type of main circuit

Other

Lifespan, mechanical

20000 operations

Overvoltage category

III

Degree of protection (IP), front side

IP40 (with insulating surround)

IP66 (with door coupling rotary handle)

Degree of protection (terminations)

IP10 (tunnel terminal)

IP00 (terminations, phase isolator and strip terminal)

Number of poles

Three-pole

Terminal capacity (copper strip)

Max. 9 segments of 9 mm x 0.8 mm at box terminal

Min. 2 segments of 9 mm x 0.8 mm at box terminal

Lifespan, electrical

5000 operations at 690 V AC-3

7500 operations at 415 V AC-3

7500 operations at 400 V AC-3

Functions

Short-circuit protection

Shock resistance

20 g (half-sinusoidal shock 20 ms)

Rated operational current for specified heat dissipation (I_n)

26 A

Short-circuit release non-delayed setting - max

338 A

Short-circuit release non-delayed setting - min

208 A

Handle type

Rocker lever

Instantaneous current setting (I_i) - max

338 A

Instantaneous current setting (I_i) - min

208 A

Number of operations per hour - max

120

Overload current setting (I_r) - max

0 A

Overload current setting (I_r) - min

0 A

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at

400/415 V, 50/60 Hz

50 kA

Rated short-circuit breaking capacity I_{cs} (IEC/EN 60947) at 440 V, 50/60 Hz

50 kA

Standard terminals

Box terminal

Rated operating voltage U_e (UL) - max

480 Y / 277 V

Release system

Thermomagnetic release

Short-circuit total breaktime

< 10 ms

Terminal capacity (aluminum solid conductor/cable)

16 mm² (1x) at tunnel terminal

Terminal capacity (control cable)

16 mm² - 18 mm² (2x)

14 mm² - 18 mm² (1x)

Terminal capacity (copper busbar)

M6 at rear-side screw connection

Max. 16 mm x 5 mm direct at switch rear-side connection

Min. 12 mm x 5 mm direct at switch rear-side connection

Terminal capacity (copper solid conductor/cable)

6 mm² - 12 mm² (1x) at box terminal

6 mm² - 12 mm² (1x) direct at switch rear-side connection

6 mm² (1x) at tunnel terminal

6 mm² - 9 mm² (2x) direct at switch rear-side connection

Terminal capacity (copper stranded conductor/cable)

4 mm² - 2/0 mm² (1x) at box terminal

4 mm² - 3/0 mm² (1x) at tunnel terminal

4 mm² - 2/0 mm² (1x) direct at switch rear-side connection

Rated short-circuit breaking capacity I_{cu} (IEC/EN 60947) at 400/415 V, 50/60 Hz

50 kA

Rated impulse withstand voltage (U_{imp}) at auxiliary contacts

6000 V

Rated impulse withstand voltage (U_{imp}) at main contacts

6000 V

Power loss

2 W



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)