

2-332095-2 ✓ ACTIVE


TE Internal #: 2-332095-2

4.52 mm [.178 in] Socket Length, 1.04 mm [.041 in] PCB Hole,  
Knockout Bottom, .081 – .162 mm<sup>2</sup> Wire, 28 – 25 AWG, Cable-to-  
Board, Pin Sockets

[View on TE.com >](#)



Connectors > Socket Connectors > Pin Sockets > Miniature Spring Sockets: Knockout Bottom Beryllium Copper, 3A



Socket Length: 4.52 mm [.178 in]

PCB Hole Diameter: 1.04 mm [.041 in]

Socket Sleeve Style: **Knockout Bottom**

Wire Size: 28 – 25 AWG

[All Miniature Spring Sockets: Knockout Bottom Beryllium Copper, 3A \(4\)](#)

## Features

### Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Socket Sleeve Style	Knockout Bottom
Connector System	Cable-to-Board
Sealable	No

### Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

### Body Features

Sleeve Plating Material	Gold Flash over Nickel
Sleeve Material	Copper

### Contact Features

Contact Spring Plating Material	Gold
Contact Base Material	Beryllium Copper
Contact Mating Area Plating Material Thickness	30 μm[30 μin]
Contact Spring Plating Thickness	.762 μm[30 μin]

Contact Current Rating (Max)	3 A
------------------------------	-----

### Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Termination Method to Wire & Cable	Solder
------------------------------------	--------

Insertion Method	Hand/Semi-Automatic
------------------	---------------------

### Dimensions

PCB Thickness (Recommended)	.79 – 3.18 mm [.031 – .125 in]
-----------------------------	--------------------------------

Socket Length	4.52 mm [.178 in]
---------------	-------------------

PCB Hole Diameter	1.04 mm [.041 in]
-------------------	-------------------

Wire Size	28 – 25 AWG
-----------	-------------

Mating Pin Diameter Range	.33 – .51 mm [.013 – .02 in]
---------------------------	------------------------------

### Usage Conditions

Operating Temperature Range	-65 – 125 °C [-85 – 257 °F]
-----------------------------	-----------------------------

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

### Packaging Features

Packaging Method	Bag, Loose Piece
------------------	------------------

Packaging Quantity	2000
--------------------	------

### Other

Spring Material	Beryllium Copper
-----------------	------------------

### Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
--	---

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability

Pin-in-Paste capable to 260°C

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # CAT-377-MSSCB3  
Mini Spring Sockets: Closed Bottom,  
3A



TE Part # 1-5332095-9  
SOCKET,MIN-SPR W/KO SN-AU S-1

## Customers Also Bought



TE Part #50863  
SOCKET,MIN-SPR AU-AU SER-2



TE Part #50863-4  
SOCKET,MIN-SPR AU-AU SER-2



TE Part #62638-1  
RING TONGUE 22-20 AWG TPBR



TE Part #2-332095-1  
SOCKET,MIN-SPR AU SER-1



TE Part #CAT-104MTA-NTPNR  
MTA Receptacle: Nylon, Tin Plated,  
2.54 mm



TE Part #CAT-104MTA-PLSCC  
Polyester PCB Connector Covers: 2.54  
mm, MTA 100



TE Part #2-1879501-9  
CRGH2512 5% 15R 2W



TE Part #5050871-1  
SOCKET,MIN-SPR W/H SN-AU SER-5

## Documents

## Product Drawings

SOCKET,MIN-SPR W/KO AU SER-1



English

---

**CAD Files**

**3D PDF**

English

**Customer View Model**

[ENG\\_CVM\\_2-332095-2\\_AA.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_2-332095-2\\_AA.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_2-332095-2\\_AA.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Product Specifications**

**Application Specification**

English