



Main

Range of product	Ovalis C Series
Product or component type	TV socket
Device presentation	Mechanism with fixing frame
TV socket type	Individual socket
Type of packing	Paint cover
Sale per indivisible quantity	1
Condition of use	Indoor

Complementary

Device mounting	Flush
TV connector	Male IEC 9.52 mm
Path attenuation	1.5 dB TV signal5...1800 MHz 2.5 dB TV signal1800...2150 MHz
Number of inputs	1
Fixing mode	By screws By claws
Colour tint	White (RAL 9003)
Surface finish	Matt
Surface treatment	Antibacterial
Connections - terminals	Screw terminals
Shape of screw head	Pozidriv No 1
Wire stripping length	8 mm
Type of cable	Coaxial
Cable outer diameter	7 mm
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame Zinc alloy: casing
Height	71 mm
Width	71 mm
Depth	34.1 mm
Embedding depth	18.1 mm
Net weight	0.041 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...45 °C
Standards	EN 50083-4
IK degree of protection	IK04
IP degree of protection	IP21D
Environmental characteristic	Bleach Liquid soap Window-cleaning fluid Alcohol Acetone Oil UV resistant Petrol

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
Minimum percentage of recycled plastic content	0