Parker Product Datasheet



The Global 56 metric series replaces the 55/58 metric series. It is shorter, more compact, and is 20% lighter than comparable fittings.

PART NUMBER: 10656-4-4-SM
SHAPE: Straight
CONNECTION 2 SIZE: 7/16'-20 UNF
BODY MATERIAL: Steel
CONNECTION 1 HOSE INSIDE DIAMETER: 1/4' (I.D.)
CONNECTION 2 TYPE: Female JIC 37° - Swivel

PRODUCT OVERVIEW

The new and improved Global 56 Series consolidates the 55 Series and the 58 Series into one. The 56 Series is shorter and more compact than the 55/58 Series Fittings, allowing for a system weight reduction of up to 20% and easier routing of assemblies during installation in tight, condensed spaces. In addition, the crimping process for the 56 Series is simpler, faster and safer since the sleeve is crimped at full length; therefore, no marking is necessary. Check crimpsource for the most up-to-date die and crimping recommendations. http://www.parker.com/crimpsource

Markets:

• Industrial

• Mobile Equipment

• Transportation

Features/Benefits:

• Consolidation of two series into one (55 and 58 = 56), thus reducing the customer inventory

• Shorter and more compact than 55/58 Series for easier routing of assemblies in tight installation areas; short length may allow use of hose routing to replace current elbow fittings

• Full length crimp of the sleeve (no marking of crimp length needed); therefore easier, safer and faster crimping in comparison to 55 Series

• Weight reduction up to 20%

• Global part numbering with metric & inch hex and end connections to allow for global availability

• Current 55 Series dies are qualified and can be used with the 56

Applications:

• Medium pressure hydraulic applications

• Agricultural equipment

• Construction

• Lubricating oils

• Material Handling equipment

• Machine tools

• Waste and refuse trucks

• Utility equipment

TECH SPECIFICATIONS

TUBE OUTSIDE DIAMETER	4 mm
APPLICATION	Agriculture Equipment
BODY MATERIAL	Steel

CONFIGURATION	Hose to Port
APPLICATION	Machine Tools
HEX SIZE 1	14 mm (see drawing legend J)
TECHNOLOGY	Fluid & Gas Handling
SPECIFICATIONS MET	ISO 12151-5-SWS
FITTING LENGTH	52 mm (see drawing legend A)
APPLICATION	Medium Pressure Hydraulics
DIVISION	Polymer Hose Division Europe
HEX SIZE 2	11 mm (see drawing legend H)
CONNECTION 2 SIZE	7/16'-20 inch Thread
CONNECTION LENGTH	27 mm (see drawing legend B)
CONNECTION 1 SIZE	1/4 inch Hose I.D.
SHAPE	Straight
APPLICATION	Construction Equipment
CONNECTION 1 SIZE	-4 (Size)
COATING	Chromium 6 Free-plated
PRODUCT TYPE	Hose Fittings
CONNECTION 1 SIZE	6.4 mm Hose I.D.
APPLICATION	Material Handling
PORT TYPE	DKJ
BRAND	Parker
INDUSTRY	Transportation
CONNECTION 1 TYPE	Hose
INDUSTRY	Off-road Machinery
DIVISION	Polymer Hose Division Europe
FOR FLUID TYPE	Water
FOR FLUID TYPE	Oil

MAXIMUM OPERATING PRESSURE	410 bar
CONNECTION 2 TYPE	Female
MAXIMUM OPERATING PRESSURE	41.0 MPa
INDUSTRY	Industrial Manufacturing Equipment
CONNECTION 2 TYPE	Swivel
FOR FLUID TYPE	Air
CONNECTION 2 TYPE	JIC 37°
FOR FLUID TYPE	Chemicals
FOR FLUID TYPE	Hydraulic Fluids