

Thermal overload relay, TeSys Deca, 690VAC, 0.63 to 1A, 1NO+1NC, class 20, screw clamp

LRD05L

### Main

Range	TeSys TeSys Deca	
product name	TeSys LRD TeSys Deca	
Product or component type	Differential thermal overload relay	
Device short name	LRD	
Relay application	Motor protection	
Product compatibility	LC1D12 LC1D25 LC1D18 LC1D38 LC1D09 LC1D32	
Network type	DC AC	
Thermal overload class	Class 20 conforming to IEC 60947-4-1	
Thermal protection adjustment range	0.631 A	
[Ui] rated insulation voltage	Power circuit: 600 V conforming to CSA Power circuit: 600 V conforming to UL Power circuit: 690 V conforming to IEC 60947-4-1	

## Complementary

Network frequency	0400 Hz	
Mounting support	Plate, with specific accessories Rail, with specific accessories Under contactor	
Tripping threshold	1.14 +/- 0.06 Ir conforming to IEC 60947-4-1	
Auxiliary contact composition	1 NO + 1 NC	
[Ith] conventional free air thermal current	5 A for signalling circuit	
Permissible current	3 A at 120 V AC-15 for signalling circuit 0.22 A at 125 V DC-13 for signalling circuit	
[Ue] rated operational voltage	690 V AC 0400 Hz for power circuit conforming to IEC 60947-4-1	
Associated fuse rating	4 A gG for signalling circuit 4 A BS for signalling circuit	
[Uimp] rated impulse withstand voltage	6 kV	
Phase failure sensitivity	Tripping current 130 % of Ir on two phase, the last one at 0	
Control type	Red push-button: stop Blue push-button: reset	

Temperature compensation	-2060 °C	
Connections - terminals	Control circuit: screw clamp terminals 2 cable(s) 12.5 mm² flexible without cable end	
	Control circuit: screw clamp terminals 2 cable(s) 12.5 mm² flexible with cable end	
	Control circuit: screw clamp terminals 2 cable(s) 12.5 mm² solid without cable end Power circuit: screw clamp terminals 1 cable(s) 1.510 mm² flexible without cable end	
	Power circuit: screw clamp terminals 1 cable(s) 14 mm² flexible with cable end	
	Power circuit: screw clamp terminals 1 cable(s) 16 mm² solid without cable end	
Tightening torque	Control circuit: 1.7 N.m - on screw clamp terminals Power circuit: 1.7 N.m - on screw clamp terminals	
Height	66 mm	
Width	45 mm	
Depth	76 mm	
Net weight	0.144 kg	

## **Environment**

Climatic withstand	conforming to IACS E10	
IP degree of protection	IP20 conforming to IEC 60529	
Ambient air temperature for operation	-2060 °C without derating conforming to IEC 60947-4-1	
Ambient air temperature for storage	-6070 °C	
Mechanical robustness	Shocks: 15 Gn for 11 ms conforming to IEC 60068-2-7 Vibrations: 3 GN conforming to IEC 60068-2-6	
Dielectric strength	1.89 kV at 50 Hz conforming to IEC 60947-1	
Standards	EN/IEC 60947-4-1 EN/IEC 60947-5-1 UL 60947-4-1 UL 60947-5-1 CSA C22.2 No 60947-4-1 CSA C22.2 No 60947-5-1 EN 50495	
Product certifications	IEC UL CSA EAC ABS ATEX INERIS UKCA	

# **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.000 cm
Package 1 Width	8.000 cm
Package 1 Length	10.000 cm
Package 1 Weight	175.000 g
Unit Type of Package 2	S02
Number of Units in Package 2	12
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm

Package 2 Weight 2.540 kg

## **Contractual warranty**

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

<b>⊘</b> Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	13
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

S Materials and Packaging		
Packaging made with recycled cardboard	Yes	
Packaging without single use plastic	Yes	
EU RoHS Directive	Compliant	
SCIP Number	224fb0ea-2bc1-482e-b6b4-c1bdd9779659	
REACh Regulation	REACh Declaration	

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins