

3-644565-6

× OBSOLETE

TE Internal #: 3-644565-6

TE Internal Description: 06P MTA100 CONN ASSY F/T 28AWG

Nylon Tin Plated Receptacle: 2.54 mm, with Mating Alignment, MTA 100

[View on TE.com >](#)



All Nylon Tin Plated Receptacle: 2.54 mm, with Mating Alignment, MTA 100 (127)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Customers Also Bought

TE Part #9-1879132-4
RN 0402 21K 0.1% 10PPM 5K RL

TE Part #8-1879126-9
RN 0402 226R 0.1% 10PPM 1K RL

TE Part #1734577-1
MOD-JK,8P8C,SHD W/LED, G/Y,6U"

TE Part #5650948-5
ASSY,PIN,EUROCARD,TYPE C/2,LEA

TE Part #7-2176092-5
RP 2A 0.25W 4K53 0.1% 25PPM 1K RL

TE Part #8-1879215-4
CPF 0402 34K 0.1% 25PPM 1K RL

TE Part #2-2176421-6
TLRP 2512 2.0W R047 1% 25PPM 4K RL

TE Part #5-1614884-2
CPF 0805 330R 0.1% 25PPM 1K RL

TE Part #T4040034041-000
M8.MLE.PNLREAR.4POS.STR
PCBSHLD

TE Part #4-1462037-8
IM07JR=IM RELAY 200mW 24V

Documents

Product Drawings

06P MTA100 CONN ASSY F/T 28AWG

English

CAD Files

Customer View Model

ENG_CVM_CVM_3-644565-6_E.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-644565-6_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-644565-6_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

English