

## Features

- Maximum operating pressure is 30 bar.
- Operating temperature range -20°C to +100°C.
- Material: Steel / Plastic with Nickel- and Zinc plated Finish
- Single Shut Off (One side is with valve)
- DN5.5
- ISO 6150-B-12
- Industrial Interchangeable 1/4"
- 1-Stage
- Compatible with:  
Industrial interchange 1/4"  
TST 024  
PARKER - RECTUS 23  
CEJN 310  
HANSEN 3000  
PARKER 20  
ATLAS COPCO QIC 08  
US-MIL-SPEC-C-4109

## RS PRO Pneumatic Quick Connect Coupling

RS Stock No.: 0325561



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

### RS PRO Series 23.06 Quick Connect Couplings

Pneumatic quick-connect coupling connectors are found across industry in pneumatic systems as diverse as robotic assembly lines and other equipment.

1-Stage coupling. Simply pressing the button once starts a fully automatic disconnection process: closure of the upstream compressed air circuit, decompression of the downstream circuit, automatic disconnection of the plug as soon as the pressure is low enough.


- Maximum operating pressure is 30 bar.
- Operating temperature range -20°C to +100°C.
- Material: Steel / Plastic with Nickel- and Zinc plated Finish
- Single Shut Off (One side is with valve)
- DN5.5
- ISO 6150-B-12
- Industrial Interchangeable 1/4"
- 1-Stage
- Compatible with:
 

Industrial interchange 1/4"	TST 024	PARKER - RECTUS 23
CEJN 310	HANSEN 3000	PARKER 20
ATLAS COPCO QIC 08	US-MIL-SPEC-C-4109	


## Specifications

Manufacturer Series	023.06
Coupling Type	Quick Connect Coupling Socket
Connection Standard	DN 5.5 ISO 6150-B-12 & Industrial Interchange 1/4"
Connection Standard Compatible With	Industrial interchange 1/4"; TST 024; PARKER - RECTUS 23; CEJN 310; HANSEN 3000; PARKER 20; ATLAS COPCO QIC 08; US-MIL-SPEC-C-4109
Minimum Operating Temperature	-20°C
Maximum Operating Temperature	+100°C
Maximum Operating Pressure	30bar
Flow	1-Stage
Flow Direction & Sealing	Self-sealing coupling
Material	Steel, Plastic
Finish	Nickel, Zinc Plated
Connection Type	Threaded
Thread Size	1/8 in
Thread Standard	NPT
Thread Gender	Male
Coupling Gender	Female
Threaded Connection	NPT 1/8 Male
Seal material	Nitrile Rubber
Hose Barb Connection	N/A

## Specifications



Dimensions (mm)		
SW	L	ØD
22	61.4	27.5





### Material Code

A = Steel Zinc Plated

B = Steel

C = Plastic

S = Steel Nickel Plated



## Series 23.06 Quick Connect Couplings




0 - 30 bar  
(0-435 PSI)



-20° to +100°C (NBR)  
-4° to +212°F

Shut Off  
Type



OM 200 - 00700  
02306GC00M

1 - STAGE

DN

5.5 mm