



**FAG****62201-A-2RSR-C3**

Deep groove ball bearing

Deep groove ball bearing 622...-A-2RSR,
single row, steel sheet metal cage

Technical information



Your current product variant

Changed internal design	A	Design variant A
Sealing	2RSR	Contact seal on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	Lubricating grease	
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	12 mm	Bore diameter
D	32 mm	Outside diameter
B	14 mm	Width
C _r	6,890 N	Basic dynamic load rating, radial
C _{0r}	3,090 N	Basic static load rating, radial
C _{ur}	243 N	Fatigue load limit, radial
n _G	14,700 1/min	Limiting speed
≈m	0.049 kg	Weight



Mounting dimensions

$d_{a\ min}$	16.2 mm	Minimum diameter shaft shoulder
$D_{a\ max}$	27.8 mm	Maximum diameter of housing shoulder
$r_{a\ max}$	0.6 mm	Maximum fillet radius

Dimensions

$r_{\ min}$	0.6 mm	Minimum chamfer dimension
D_1	26.11 mm	Shoulder diameter outer ring
D_2	27.93 mm	Caliber diameter outer ring
d_1	18.25 mm	Shoulder diameter inner ring

Temperature range

$T_{\ min}$	-20 °C	Operating temperature min.
$T_{\ max}$	100 °C	Operating temperature max.

Calculation factors

f_0	12.3	Calculation factor
-------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides