



**Part Number :** [1201080620](#)  
**Product Description :** Micro-Change (M12)  
Double-Ended Cordset, 4 Poles, D-Coded,  
Male (90°) to Female (Straight), 24 AWG, Teal  
TPE Cable, 0.50m (1.64') Length  
**Series Number :** 120108  
**Status :** Active  
**Product Category :** Circular Industrial  
Cordsets  
**Engineering Number :** E11A03204M005



Documents & Resources

Drawings  
[1201080620\\_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	120108
Description	Micro-Change (M12) Double-Ended Cordset, 4 Poles, D-Coded, Male (90°) to Female (Straight), 24 AWG, Teal TPE Cable, 0.50m (1.64') Length
IP Rating	IP67
Performance Category	5e
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	78172552303

### Agency

UL	E361772
----	---------

### Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

### Physical

Cable Diameter	6.10mm (.240")
Cable Length	0.50m (1.64')
Color - Cable Jacket	Teal
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	D-Coded
LED Indicator	None

Material - Cable Jacket	TPE
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	90° to Straight
Poles	4
Temperature Range - Operating	-20° to +75°C
Wire/Cable Type	Unshielded TPE/AWM 2463
Wire Size (AWG)	24