

Pilot light, Harmony XB7, round Ø22 mm, green, bulb BA 9 s, 230 V, screw clamp terminals

XB7EV73P

! Discontinued on: 9 Feb 2023

① Discontinued

EAN Code: 3389110839647

Main

Range of product	Harmony XB7
Product or component type	Pilot light
Device short name	XB7
Mounting diameter	22 mm
Sale per indivisible quantity	10
Operator additional information	With plain lens
Light source	Incandescent
Device presentation	Monolithic product

Complementary

o o mpromontar y		
Height	29 mm	
Width	29 mm	
Depth	54 mm	
Terminals description ISO n°1	(X1-X2)PL	
Net weight	0.02 kg	
Overvoltage category	Class II conforming to IEC 60536	
Device mounting	Fixing hole - diameter: 22.5 mm 22.3 +0.4/0 conforming to IEC 60947-5-1	
Fixing center	>= 30 x 40 mm (support panel) metal - thickness: 16 mm >= 30 x 40 mm (support panel) plastic - thickness: 26 mm	
Fixing mode	Fixing nut beneath head: 22.4 N.m	
Shape of signaling unit head	Round	
Cap/operator or lens colour	Green	
Connections - terminals	Faston connectors, connection size: 6.35×0.8 mm conforming to IEC 60947-1 Forked type tag connectors, connection size: 6.5 mm conforming to IEC 60947-1 Screw clamp terminals, $\le 2 \times 1.5$ mm² with cable end conforming to IEC 60947-1 Screw clamp terminals, $1 \times 0.222 \times 2.5$ mm² without cable end conforming to IEC 60947-1	
Tightening torque	0.81.2 N.m conforming to IEC 60947-1	
Shape of screw head	Cross compatible with JIS No 1 screwdriver Cross compatible with Philips no 1 screwdriver Cross compatible with pozidriv No 1 screwdriver Slotted compatible with flat Ø 4 mm screwdriver Slotted compatible with flat Ø 5.5 mm screwdriver	
[Ui] rated insulation voltage	250 V (pollution degree 3) conforming to IEC 60947-1	

[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-1
Signalling type	Steady
Bulb base	BA 9s
Light block supply	Direct through resistor <2.6 W 130 V
[Us] rated supply voltage	230 V AC at 50/60 Hz
Supply voltage limits	195264 V AC
Service life	2000 h at rated voltage and 25 °C
Compatibility code	XB7

Environment

Protective treatment	тн
Ambient air temperature for storage	-4070 °C
Ambient air temperature for operation	-2555 °C
IP degree of protection	IP20 (rear face) conforming to IEC 60529 IP54 (front face) conforming to IEC 60529
NEMA degree of protection	NEMA 12
Standards	UL 508
	CSA C22.2 No 14
	IEC 60947-1
	IEC 60947-5-1
	JIS C8201-5-1
	JIS C8201-1
Vibration resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27
Electromagnetic compatibility	Disturbing field emission class B conforming to IEC 55011

Packing Units

r doming office	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm
Package 1 Width	10.000 cm
Package 1 Length	5.000 cm
Package 1 Weight	20.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	7.000 cm
Package 2 Width	10.000 cm
Package 2 Length	15.000 cm
Package 2 Weight	206.000 g
Unit Type of Package 3	S01
Number of Units in Package 3	100
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm

Package 3 Length	40.000 cm
Package 3 Weight	2.296 kg

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	97
Environmental Disclosure	Product Environmental Profile

Use Better

⊗ Materials and Substances		
Packaging made with recycled cardboard	No	
Packaging without single use plastic	No	

Use Again


○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

XB7EV73P

Dimensions Drawings

Pilot Light with Screw Terminal

Dimensions




e Support panel thickness: 1 to 6 mm/0.4 to 0.24 in. (metal), 2 to 6 mm/0.8 to 0.24 in. (plastic).

XB7EV73P

Mounting and Clearance


Mounting

Diameter of Finished Fixing Holes




- (1) Minimum value.
- (2) 40 mm/1.58 in. for Emergency switching off pushbutton only.
- (3) Standard value: Ø 22.3 (0; + 0.4) mm/Ø 0.88 (0; + 0.02) in.

Faston Clip Connection



"U" Type Tag Connection




- (1) 6.5 mm/0.26 in. recommended, 7 mm/0.28 in. max.
- (2) M3 screw clamp terminal.

Product datasheet

XB7EV73P

Connections and Schema

Wiring Diagram



(1) bulb BA 9s