

DDR4 DIMM

TE Internal #: 2309410-3

Small Outline (SO), 5.2 mm [.205 in] Stack Height, Right Angle
Module Orientation, 200 / 260 Position, DDR4 DIMM, SO DIMM
Sockets

[View on TE.com >](#)



Connectors > Socket Connectors > Memory Sockets > SO DIMM Sockets > DDR4 SO DIMM Sockets



DRAM Type: **Small Outline (SO)**
Stack Height: **5.2 mm [.205 in]**
Module Orientation: **Right Angle**
Number of Positions: **200, 260**
Centerline (Pitch): **.5 mm [.02 in]**

[All DDR4 SO DIMM Sockets \(39\)](#)

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Cable-to-Board
DRAM Type	Small Outline (SO)

Configuration Features

Number of Keys	1
Number of Rows	2
Module Orientation	Right Angle
Number of Positions	200, 260

Electrical Characteristics

DRAM Voltage	1.2 V
--------------	-------

Signal Characteristics

SGRAM Voltage	1.2 V
---------------	-------

Body Features

Retention Post Location	Both Ends
Retention Post Material	Copper Alloy



Latch Material	High Temperature Thermoplastic
Ejector Type	Locking
Ejector Location	Both Ends
Connector Profile	Low

Contact Features

Contact Current Rating (Max)	.5 A
Contact Underplating Material	Nickel
Memory Socket Type	Memory Card
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Gold Flash
Contact Mating Area Plating Material	Gold (Au)
Contact Mating Area Plating Material Thickness	.254 μm[10 μin]

Termination Features

Insertion Style	Cam-In
Termination Method to PCB	Surface Mount

Mechanical Attachment

Connector Mounting Type	Board Mount
PCB Mount Retention Type	Solder Peg
Mating Alignment Type	Reverse Keying
PCB Mount Retention	With

Housing Features

Housing Material	High Temperature Thermoplastic
Housing Color	Black
Centerline (Pitch)	.5 mm[.02 in]

Dimensions

Stack Height	5.2 mm[.205 in]
Row-to-Row Spacing	8.2 mm[.322 in]

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards



UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	800
Packaging Method	Tape & Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





Also in the Series

DDR4 DIMM

DIMM Sockets(25)

SO DIMM Sockets(39)

Customers Also Bought

TE Part #5-102570-3
10 MODII HDR DRRA SHRD LF

TE Part #3-1939756-6
.5FHP08H,220,S,GIG,30/Sn,HT,NS

TE Part #2309413-3
DDR4 SODIMM 260P 9.2H STD

TE Part #2-2013311-1
EMBOSS TAPE DDR3 204P 9.2H RVS

TE Part #2-2013298-1
EMBOSS TAPE DDR3 204P 8H RVS

TE Part #3-6318491-6
.5FHP08H,220,S,GIG,08/Sn,HT,NSYes

TE Part #2023308-3
(LCEDI) SR interface Rec conn 40pos

TE Part #2-2013310-2
EMBOSS TAPE DDR3 204P 9.2H STD

TE Part #2-2013310-1
EMBOSS TAPE DDR3 204P 9.2H STD

TE Part #244837-E
SMCQ 26 M AB VV 8-13 CL * H007 137 E005

Documents

Product Drawings

DDR4 SODIMM 260P 5.2H RVS

English

CAD Files

3D PDF

3D



Customer View Model

[ENG_CVM_CVM_2309410-3_1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2309410-3_1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2309410-3_1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English