

■ Product Type Sealed Rocker Switches

Product Series
L-Series

The L-Series snap-in rocker switches offer countless unique options including choices for ratings, circuits, colors, illuminations and laser etched legends. These single or double pole switches feature a broad choice of actuator styles, colors, and lenses. Neatly proportioned, the L-Series rocker switch fits into industry standard mounting holes of 1/734' x .867 & and 44.0mm x 22.0mm. Twelve terminals offer an extensive range of switch and lamp circuit options, including LED or incandescent illumination. An optional plug-in terminal connector enables pre-wiring of wire harness.

The L-Series switches, with sealed front panel components, are IP67 certified, and able to withstand temperatures from -40°C to +85°C. These switches are vibration, shock, thermoshock, moisture and salt spray resistant.

Certifications
Number of Poles

No Agency Listings 1-2 pole Ratings .4VA @ 28VDC Resistive

10A 250VAC 15A 125VAC

1/2HP

No Agency Listings

15A 12V 15A 24V 20A 18V 20A 12V 20A 6V 20A 3V

Dielectric Strength 1250V RMS opposite polarity

3750V RMS between live parts and operator accessible surface

Insulation Resistance 50 megohms (minimum)

Base Material Polyester

Actuator Style Convex rocker

Illuminated convex rocker with large lens Illuminated convex rocker with bar lens(es)

Illuminated convex rocker with combination large and bar lenses

Convex locking rocker with or without lens

Actuator Material Lens - Polycarbonate

Actuator - Nylon 66 reinforced

Laser etching with polycarbonate actuator

Terminal Options .250 QC Tabs

.187 QC Tabs

Mounting Method Snap-In

Mounting Hole Dimensions .867" x 1.734"; 22mm x 44mm

Value Added Custom colors and legends available

Progressive circuits

Optional terminal connector

Hole Plug



L-Series Sealed Rocker Switches



Making the right connections has never been easier — with the L-Series Rocker Switch from Carling Technologies. Not only does this innovative switch offer total design flexibility, it has set new standards for both performance and reliability. It's IP67 certified, and able to withstand temperatures from -40°C to +85°C. Features include countless switch and lamp circuit combinations, LED illuminated lenses or laser etched rockers, as well as hundreds of legend choices and several accessories.

Eliminates need for retooling

Neatly proportioned, our L-Series fits into industry standard mounting holes of 1.734" x .867" and 44.0mm x 22.0mm.

Withstands extreme temperatures

Roller pin mechanism eliminates need for lubricants, so it can withstand from - 40°C to +85°C.

Integrates easily into your system

You can choose from a variety of termination options, including .250 TAB QC & .187 TAB QC.

Ensures greater shock protection

Welded lamp connection and one-piece internal, jumperless terminal withstand extreme shock and vibration.

Maximizes your design flexibility

Twelve terminals offer you an extensive range of switch and lamp circuit options, including LED or incandescent illumination.



60



Electrical

20 amps, 4-14 VDC 15 amps, 15-28 VDC

Dielectric Strength 1250 Volts RMS between pole to

pole

3750 Volts RMS between live parts

and accessible surfaces

Insulation Resistance . . . 50 Megohms

voltage and current

gold

Terminals Brass or copper/silver plate

3/16" (4.76mm) & 1/4" (6.3mm) Quick Connect terminations standard.

Mechanical

Endurance 250,000 cycles minimum

Physical

Lighted Incandescent - rated 10,000 hours LED - rated 100,000 hours 1/2 life (LED is internally ballasted for voltages to 24 VDC)

Seals Rocker, base & bracket are sealed.

Base Polyester blend rated to 85°C with a

flammability rating of 94VO.

Actuator Nylon 66 Reinforced, rated to 105°C (modular lens). Locking rocker, standard rocker & paddle. Laser etching

with a polycarbonate actuator.

Lens Polycarbonate rated at 100°C. Front

snap-in.

Connector Nylon 66 rated at 85°C. Polarized.

Actuator Travel (Angular Displacement)

2 position 26°

3 positions 13° from center

Environmental

Environmental IP67, representing an index of

protection as applied to electrical equipment in accordance with IEC 529, BS 5490, DIN 400 50 & NFC

20 010.

Corrosion Resistance . . . MFG Class III per ASTM B-827 &

B-845, Method H, with 3 years

exposure.

Operating Temperature . . . -40° C to + 85° C

Vibration 1 Per Mil-Std 202F, Method 204D Test

Condition A 0.06 DA or 10G's 10-500 Hz. Tested with VCH connector. Test criteria - No loss of circuit during test and pre and post test contact resist-

ance.

Vibration 2 Resonance search

24-50 Hz 0.40 DA 50-2000 ±10 G's peak

Results Horizontal Axis 3-5 G's max.

Random

24 Hz 0.06 PSD-Gsq/Hz 60 Hz 0.50 100 Hz 0.50 200 Hz 0.25

200 Hz 0.025 2000 Hz 0.025 No loss of circuit during test; <10μ

chatter. lock Per Mil-Std 202F. Method 213B. Test

Condition K @ 30G's. Tested with VCH connector. Test criteria - No loss of circuit during test, pre, and post test contact resistance.

Salt Spray Per Mil-Std 202F, Method 101D, Test

Condition A, 48 Hrs.

Thermal Shock Per Mil-Std 202F, Method 107F, Test

Condition A, -55°C to 85°C. Test criteria - pre and post test contact


resistance.

Moisture Resistance Per Mil-Std 202F, Method 106F, Test

Criteria - pre and post test contact

resistance.

Mounting Specifications



MOUNTING HOLE

Panel Thickness Range Acceptable Panel Thickness .030 to .156 (.76mm to 3.96mm)

Recommended:

.030, .062, .093, .125 and .156



























Circuit

Rating

Termination Illumination Lamp

Lamp

Bracket

Actuator

10 Lens Style & Color

Lens Style Legend & Color

13 Leaend Orientation

Actuator Lens Legend

1 SERIES

2 CIRCUIT²

Terminal Orientation

() - momentary

SP - single pole - uses terminals 1, 2 & 4. DP - double pole uses terminals 5 , 6 & 8. Terminals 9, 10, 11 & 12 for lamp circuit only.

,		□′					
<i>Posit</i> SP	ion: DP	1 2 & 4, 6 & 8	2 Connected Terminals	3 1 & 2, 5 & 6			
	21	ON	NONE	OFF			
	22	(ON)	NONE	OFF			
	23	ON ON	NONE	(OFF)			
-	24	ON	NONE	ON ON			
	25	ON	NONE	(ON)			
	26	ON	OFF	ON			
	27	ON	OFF	(ON)			
	28	(ON)	OFF	(ON)			
		WITH JUMPER TER		(014)			
30	0110	(2,4&5),(1,6&8)	OFF, OFF	(1,2&8),(4,5&6)			
31		1,2&5	2,3&7	2,4&8			
	3RFS	SSIVE CIRCUITS	2,007	2,100			
51		3&4	2&3	1&2			
52		3&4	2&3	OFF			
53		(3&4)	2&3	1&2			
54		(3&4)	2&3	OFF			
55		(3&4)	2&3	(1&2)			
56		(3&4)	2&3	(OFF)			
57		3&4	2&3	(OFF)			
58		2&4	2&3	1&2			
61		3&4,7&8	2&3,6&7	1&2,5&6			
62		3&4,7&8	2&3,6&7	OFF, OFF			
63		(3&4),(7&8)	2&3,6&7	1&2,5&6			
64		(3&4),(7&8)	2&3,6&7	OFF,OFF			
65		(3&4),(7&8)	2&3,6&7	(1&2),(5&6)			
66		(3&4),(7&8)	2&3,6&7	(OFF),(OFF)			
67		3&4,7&8	2&3,6&7	(OFF),(OFF)			
68		2&4,7&8	2&4,OFF	OFF,OFF			
69		2&4,1,7&8	2&4,OFF	OFF,OFF			
70		(2&4),(7&8)	2&4,5&7	(1&2),(5&7)			
71		(2&4),(7&8)	2&4,5&7	1&2,5&7			
72		2&4,7&8	2&4,5&7	1&2,5&7			
73		(2&4),(7&8)	2&4,OFF	OFF,OFF			
80		2&4,6&8	2&4,OFF	OFF,5&6			
HAZARD WARNING CIRCUITS							

A2

А3

.4VA @ 28VDC Resistive 20A 12V 10A 250VAC 1/2 HP, Е 15A 12V 20A 6V 15A 125VAC 1/2 HP, No Listings G В 15A 24V 20A 3V C 20A 18V

6,7&8, 3&4

6,7&8, 2&4

4 TERMINATION^{2,3,4}

.250 (6.4mm) TAB (QC) .187 (4.7mm) TAB (QC)

NONE

NONE

OFF,1&2

OFF,1&2

NOTES:

Consult factory to verify horsepower rating for your particular circuit choice.

- Custom colors are available. Consult factory.
- Circuits 30, 31, 58, 69 when used in combination with termination codes 1 and 3 are not available with rating codes 4, C, D, G or H. 2
- Termination 3 only available with rating codes 1, B, and E.
- Termination 1 not available with rating code 4.
- Not available with circuits 11-18, 51-57 and 69. 5

5 ILLUMINATION

Lamp #1:above terminals 9 & 10 end of switch.; Lamp #2 above terminals 11 & 12 end of switch. Positive (+) and negative (-) symbols apply to LED lamps only.

	<u>Lamps</u>	Illumination Type	Lamp wired to Terminals		<u>Terminals</u>	
S	None					
Α	# 1	Independent	10+	9-		
В	# 2	Independent	12+	11-		
С	# 1	Independent	10+	9-		
	&# 2</th><th>Independent</th><th>12+</th><th>9-</th><th></th><th></th></tr><tr><th>D</th><th># 1</th><th>Dependent</th><th>4+</th><th>9-</th><th></th><th></th></tr><tr><th>E</th><th># 1</th><th>Independent</th><th>10+</th><th>9-</th><th></th><th></th></tr><tr><th></th><th>&# 2</th><th>Dependent</th><th>4+</th><th>9-</th><th></th><th></th></tr><tr><th>F⁵</th><th># 1</th><th>Independent</th><th>10+</th><th>9-</th><th></th><th></th></tr><tr><th></th><th>&# 2</th><th>Dependent</th><th>8+</th><th>9-</th><th></th><th></th></tr><tr><th>G</th><th># 1</th><th>Dependent</th><th>4+</th><th>9-</th><th></th><th></th></tr><tr><th></th><th>&# 2</th><th>Independent</th><th>10+</th><th>9-</th><th></th><th></th></tr><tr><th>Н</th><th># 1</th><th>Both Independent</th><th>10+</th><th>9-</th><th></th><th></th></tr><tr><th></th><th>&# 2</th><th>(in series)</th><th></th><th></th><th></th><th></th></tr><tr><th>1</th><th># 2</th><th>Hazard</th><th>6+</th><th>10+</th><th>12-</th><th></th></tr><tr><th>2</th><th># 1</th><th>Hazard</th><th>6+</th><th>10+</th><th>12-</th><th></th></tr></tbody></table>					

6,7 LAMP (same coding for both selections)

Selection 6: above terminals 10 & 9; Selection 7: above terminals 12 & 11

	No lamp	0		.0	.0			
	Incandescent	4 3V	5 6V	6 12V	7 18V	8 24V		
	LED*	Red	Amber	Green				
	2VDC	Α	L	F				
	6VDC	В	M	G				
	12VDC	С	N	Н				
	24VDC	D	P	J				
* Consult factory for "daylight bright", blue/green and white LED options.								
	Typical aurrent draw for LED is 20mg							

Typical current draw for LED is 20ma

8 BRACKET COLOR

	Black	White	Gray	Red
Standard Bracket	1	2	3	4
Rockerguard at Lamp 1	Α	В	Ċ	D
Bockerguard at Lamp 2	F	F	G	н

9 ACTUATOR STYLE AND COLOR¹

	Black	White	Gray	Red	Laser Etched
Rocker	Α	В	C ´	D	3
Daddla	1	M	V	IV.	4

10 & 11 LENS STYLE AND COLOR

Lens color for LEDs must be clear, white, or match color of LED. Green or blue lenses are not recommended with Neon lamps.

U - NO Actuator		Z - INO I	Lens			
Clear	White	Amber	Green	Red	Blue	
1	-	В	G	M	Т	Large Transparent
-	7	С	Н	N	U	Large Translucent
3	-	D	J	Р	٧	Bar Transparent
-	9	E	K	R	W	Bar Transparent
5	Α	-	-	-	-	Laser Etch background color

12 LASER ETCH, LENS OR BODY LEGEND

00 No legend this location / no actuator
For legend options & codes, see page 69 of this catalog.


13 LEGEND ORIENTATION


No legend (used with codes 11-18 in selection 12) 0

Orientation 1 - vertical, lamp 1 on top 1

2 Orientation 2 - horizontal, lamp 1 on right 3 Orientation 3 - vertical, lamp 1 on bottom LAMP 2

Orientation 4 - vertical, lamp 1 on left





14 ACTUATOR LENS LEGEND

00 No legend this location / no actuator

For legend options & codes, see page 69 of this catalog.



Dimensional Specifications


L SERIES SHOWN WITH LASER ETCHED ACTUATOR

1.970 [50.04]


1.020 [25.91]

1.450 [36.83]


L SERIES SHOWN WITH ROCKER GUARD



L SERIES SHOWN WITH LARGE LENS AND PADDLE ACTUATOR



L SERIES SHOWN WITH BAR LENS, LOCK AND CONNECTOR




Connector


L SERIES
CONNECTOR

LC1-01 BLACK .250 TAB CONNECTOR


LC1-02 BLACK .187 TAB CONNECTOR









Hole Plug






Mounting Panel






LM3 MOUNTING PANEL PANEL OPENING SIZE: 1.90 X 3.06 [48.3mm X 77.7mm]



LM4 MOUNTING PANEL PANEL OPENING SIZE: 1.90 X 4.09 [48.3mm X 103.9mm]



LM6 MOUNTING PANEL PANEL OPENING SIZE: 1.90 X 6.15 [48.3mm X 156.2mm]