

# CA-09S1N1280DNSX - Cable connector



1243688

<https://www.phoenixcontact.com/in/products/1243688>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: CA, straight, shielded: yes, SPEEDCON, No. of pos.: 8+1, Direction of rotation: Standard, contact connection type: Socket, Solder connection, cable diameter range: 3 mm ... 14.5 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Reduced connection time with SPEEDCON fast locking system
- Solder connection: proven connection technology for various litz wires

## Commercial data

Item number	1243688
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ABRAEB
GTIN	4063151474355
Weight per piece (including packing)	96.9 g
Weight per piece (excluding packing)	96.9 g
Customs tariff number	85366990
Country of origin	DE

# CA-09S1N1280DNSX - Cable connector



1243688

<https://www.phoenixcontact.com/in/products/1243688>

## Technical data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Connection 1

Head design	Socket
-------------	--------

#### Insulating body

Coding	N
Insulation body material	PBT
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Socket
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Contact diameter <b>Power contacts</b>	2 mm
Litz wire cross-section <b>Power contacts max.</b>	2.5 mm <sup>2</sup>
Rated current <b>Power contacts</b>	20 A
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Contact diameter <b>Signal contacts</b>	1 mm
Litz wire cross-section <b>Signal contacts max.</b>	1 mm <sup>2</sup>
Nominal current per signal contact	8 A

#### Housing

Housing material	CuZn, GD-Zn
Type of locking	SPEEDCON
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

#### Seal

External cable diameter	3 mm ... 14.5 mm
-------------------------	------------------

# CA-09S1N1280DNSX - Cable connector



1243688

<https://www.phoenixcontact.com/in/products/1243688>

Seal material	NBR
---------------	-----

## Environmental and real-life conditions

Ambient conditions	
Ambient temperature (operation)	-40 °C ... 125 °C

# CA-09S1N1280DNSX - Cable connector


1243688

<https://www.phoenixcontact.com/in/products/1243688>



## Drawings

Schematic diagram



Connector pin assignment

# CA-09S1N1280DNSX - Cable connector



1243688

<https://www.phoenixcontact.com/in/products/1243688>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1243688>

cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
Power	48 V	12 A	14	-
Signal	48 V	6 A	18	-

UL Recognized Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
Power	48 V	20 A	14	-
Signal	48 V	8 A	18	-

cULus Recognized				
------------------	--	--	--	--

# CA-09S1N1280DNSX - Cable connector



1243688

<https://www.phoenixcontact.com/in/products/1243688>

## Classifications

### ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

### ETIM

ETIM 9.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121100
-------------	----------

# CA-09S1N1280DNSX - Cable connector



1243688

<https://www.phoenixcontact.com/in/products/1243688>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

# CA-09S1N1280DNSX - Cable connector

1243688

<https://www.phoenixcontact.com/in/products/1243688>



## Accessories

### SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/in/products/1607456>

Torque screwdriver, series: RC, UC, SH, SF



---

### SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/in/products/1607455>

Hook wrench, series: RC, UC, RF, SF





# CA-09S1N1280DNSX - Cable connector



1243688


<https://www.phoenixcontact.com/in/products/1243688>

## RF-Z0014 - Color coding

1620588

<https://www.phoenixcontact.com/in/products/1620588>

Color coding, color: green




---

## RF-Z0015 - Color coding

1620592

<https://www.phoenixcontact.com/in/products/1620592>

Color coding, color: orange



# CA-09S1N1280DNSX - Cable connector

1243688

<https://www.phoenixcontact.com/in/products/1243688>



## RF-Z0016 - Color coding

1620593

<https://www.phoenixcontact.com/in/products/1620593>

Color coding, color: black



---

## RF-Z0003X - Square mounting flange

1242369

<https://www.phoenixcontact.com/in/products/1242369>



Square mounting flange, Axial seal, 4xM3, flange dimensions: 35 mm x 35 mm, series: RF, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## CA-09S1N1280DNSX - Cable connector

1243688

<https://www.phoenixcontact.com/in/products/1243688>



## CA-Z0077X - Metal protective cap

1245447

<https://www.phoenixcontact.com/in/products/1245447>



Metal protective cap, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

---

## PROT-M23-SG-IT-IP20 - Plastic protective cap

1577206

<https://www.phoenixcontact.com/in/products/1577206>



Plastic protective cap, M23, series: CA, RC, RF, UC, RM

---

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.  
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420  
[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)