


Data Sheet | Item Number: 294-5075

Lighting connector; push-button, external; without ground contact; 5-pole; Lighting side: for solid conductors; Inst. side: for all conductor types; max. 2.5 mm²; Surrounding air temperature: max 85°C (T85); white

<https://www.wago.com/294-5075>



Color: white



Dimensions in mm

Field-wiring terminal block, 294 Series, Push-in

Connecting conductors is quick and easy with this field-wiring terminal block (item number 294-5075). Ensure that the strip lengths are between 8 and 9 mm when connecting conductors to this field-wiring terminal block. This product features four conductor terminals and utilizes Push-in CAGE CLAMP® and PUSH WIRE®. Push-in CAGE CLAMP® connection technology is ideal for connecting all conductor types. Solid and fine-stranded conductors with ferrules can be pushed in without needing to use any tools—all thanks to its pluggable design. Our reliable PUSH WIRE® connection offers the fastest method for clamping conductors. It utilizes the conductor's stiffness to overcome the clamping spring's contact force. The dimensions are (50 x 21.53 x 27.3) mm (width x height x depth). This field-wiring terminal block is suitable for conductor cross sections ranging from 0.5 mm² to 2.5 mm² on one side and for conductor cross sections ranging from 0.5 mm² to 2.5 mm² on the other side as well as conductor cross sections from 0.5 mm² to 2.5 mm² and from 0.5 mm² to 0.75 mm² depending on the conductor type.

Tin is used for coating the contact surfaces.

Electrical data				
Ratings per		IEC/EN 60998-1		
Overvoltage category		III	III	II
Pollution degree		3	2	2
Nominal voltage		-	-	500 V
Rated impulse withstand voltage		-	-	4 kV
Rated current		-	-	24 A

Ratings per IEC/EN – Notes	
Ratings (note)	Connection points

Ratings per		IEC/EN 60998-2-2		
Overvoltage category		III	III	II
Pollution degree		3	2	2
Nominal voltage		-	-	500 V
Rated impulse withstand voltage		-	-	4 kV
Rated current		-	-	24 A

General information	
Wiring direction	Side-entry wiring

Connection Data

Clamping units	25
Total number of potentials	5
Number of connection types	4
PE function	without PE contact

Connection 1

Connection type	External 1
Connection technology	Push-in CAGE CLAMP®
Number of connection points	2
Actuation type	Push-button
Connectable conductor materials	Copper
Solid conductor	0.5 ... 2.5 mm ² / 18 ... 12 AWG
Solid conductor; push-in termination	0.5 ... 2.5 mm ² / 18 ... 12 AWG
Stranded conductor	0.5 ... 2.5 mm ² / 18 ... 14 AWG
Fine-stranded conductor	0.5 ... 2.5 mm ² / 18 ... 14 AWG
Fine-stranded conductor; with insulated ferrule	0.5 ... 1.5 mm ² / 18 ... 16 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1.5 mm ² / 18 ... 16 AWG
Fine-stranded conductor; with ferrule; push-in termination	0.5 mm ² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches
Pole number	5
Wiring direction	Side-entry wiring

Connection 2

Connection type	Internal 2
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 2.5 mm ² / 18 ... 14 AWG
Fine-stranded conductor; with insulated ferrule	0.5 ... 1 mm ² / 18 ... 16 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1.5 mm ² / 18 ... 14 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Connection 3

Connection type	Internal 3
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 1.5 mm ² / 18 ... 16 AWG
Fine-stranded conductor; with insulated ferrule	0.5 ... 0.75 mm ² / 18 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1 mm ² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Connection 4

Connection type	Internal 4
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 0.75 mm ² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Physical data

Pin spacing	10 mm / 0.394 inches
Width	50 mm / 1.969 inches
Height	21.53 mm / 0.848 inches
Height from the surface	17 mm / 0.669 inches
Depth	27.3 mm / 1.075 inches

Mechanical data		
Marking		DA- N ⊕ L DA+
Mounting type		Snap-in foot

Material data		
Note (material data)		Information on material specifications can be found here
Color		white
Material group		IIIa
Insulation material (main housing)		Polycarbonate (PC)
Flammability class per UL94		V0
Clamping spring material		Chrome-nickel spring steel (CrNi)
Contact material		Electrolytic copper (E _{Cu})
Contact Plating		Tin
Fire load		0.23 MJ
Halogen-free		Yes
Weight		15.2 g

Environmental requirements		
Temperature stability		120 °C
T marking		T85

Commercial data		
Product Group		8 (Misc. Chassis Mount Blocks)
PU (SPU)		250 pcs
Packaging type		Foil
Country of origin		CH
GTIN		4050821098324
Customs tariff number		85369010000

Product Classification		
UNSPSC		39121409
eCl@ss 10.0		27-14-11-06
eCl@ss 9.0		27-14-11-06
ETIM 9.0		EC001284
ETIM 10.0		EC001284
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant, No Exemption
SCIP notification number (Austria)		ee7cfba0-0862-4bc9-9025-92111d271f46
SCIP notification number (Belgium)		22fb2bb9-8099-4f5d-a867-9fd811d76519
SCIP notification number (Bulgaria)		90e1b144-cfef-4f67-b3cf-d1ef2b81022c
SCIP notification number (Czech Republic)		e65e6be8-5d55-49cc-9d81-405a6138d41f
SCIP notification number (Denmark)		afa9de2f-97e1-4c00-bcfd-d5f828a7b0cc
SCIP notification number (Finland)		cf02a68b-3f57-41cf-a0e4-993dceeabac5
SCIP notification number (France)		71949a38-d3ab-4baa-b281-4f000d0f6311
SCIP notification number (Germany)		6ed59414-9fd2-47a8-b279-a38420bbe2b9
SCIP notification number (Hungary)		d1742bfd-0123-4655-b5cf-a54c7d7d8d57
SCIP notification number (Italy)		bc8819b9-a04f-466a-9614-12732a97da5f
SCIP notification number (Netherlands)		9c5b9d90-3edb-46ab-a98e-19a8c83aaf23
SCIP notification number (Poland)		36e8cc9b-3ce6-4c7c-9ab2-f5cf2be07950
SCIP notification number (Romania)		6b713ede-5570-4094-aa0d-99e469f06c66

Environmental Product Compliance	
SCIP notification number (Sweden)	d8f9b469-8d83-4e1b-8a92-b8faff1ed7ee

Approvals / Certificates

General approvals		Declarations of conformity and manufacturer's declarations
		
Approval	Standard	Certificate Name
ENEC 05 DEKRA Certification B.V.	EN 60998	2128791.01
		EU-Declaration of Conformity WAGO GmbH & Co. KG
		UK-Declaration of Conformity WAGO GmbH & Co. KG

Downloads

Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 294-5075	

Documentation

Bid Text			
294-5075	19.02.2019	xml 5.58 KB	
294-5075	13.06.2017	doc 28.50 KB	

CAD/CAE-Data

CAD data	CAE data
2D/3D Models 294-5075 	WSCAD Universe 294-5075 
	ZUKEN Portal 294-5075 

1 Compatible Products

1.1 Optional Accessories

1.1.1 Strain relief

1.1.1.1 Strain relief

Item No.: 294-370
Strain relief; for 294 Series; with snap-in mounting feet; white

Item No.: 294-375
Strain relief; for 294 Series; without snap-in mounting feet; white

1.1.1.2 Strain relief plate

Item No.: 294-364
Strain relief plate; for 294 Series; for multi-core cables; 3- to 5-pole; with secured clamp; white

Item No.: 294-384
Strain relief plate; for 294 Series; for single strands; 3- to 5-pole; with secured clamp; white

1.1.2 Tool

1.1.2.2 Operating tool

Item No.: 206-294
Disconnection tool; green

Installation Notes

Installation

5-pole – without ground contact

Snap-in foot

Drilled hole for snap-in mounting foot

Conductor termination

EUROPE
1 x 0.5 ... 2.5 mm ² "s"
1 x 0.5 ... 1.5 mm ² "s"
1 x 0.5 ... 0.75 mm ² "s"
AMERICA
1 x AWG 18 ... 14 "s"
1 x AWG 18 ... 16 "s"
1 x AWG 18 "s"
JAPAN
1 x 0.8 ... 1.6 mm diam. "s"
1 x 0.8 ... 1 mm diam. "s"
1 x 0.8 mm diam. "s"

EUROPE
2 x 0.5 ... 2.5 mm ² "s, str, f-str"
AMERICA
2 x AWG 18 ... 12 "s"
2 x AWG 18 ... 14 "s, f-str"
JAPAN
2 x 0.8 ... 2 mm diam. "s"
2 x 0.5 ... 2 mm ² str, f-str"

Internal connection:
PUSH WIRE® for internal wiring with solid conductors

External connection:
Push-in CAGE CLAMP® for field-wiring with all conductor types

Terminating five conductors per pole – solid and fine-stranded.

Externe Anschlusseite 1 2 3 4 Interne Anschlusseite

