# **Panasonic**

## Stacked Coin Type

Series: SD

■ Feature

Endurance: 70°C 1000 h

Japan




■ Recommended Applications

Memory back-up for Video, Audio, Cameras, Telephones, Printer, Data terminal, Rice cooker, Intelligent remote controller

### ■ Specifications

Category temp. range	-25 to +70°C					
Maximum Operating Voltage	5.5 V .DC					
Nominal Cap. Range	0.022 to 0.33 F					
Characteristics at Low Temperature	Capacitance change	apacitance change ±30% of initial measured value at +20°C (-25 to +70°C)				
	Internal resistance	≤ 5 times of initial measured value at +20°C (at -25°C)				
Endurance	After 1000 hours application of 5.5V. DC at +70°C, the capacitor shall meet the following limits.					
	Capacitance change	±30% of initial measured value				
	Internal resistance	≤ 4 times of initial specified value				
Shelf Life	After 1000 hours storage at +70°C without load, the capacitor shall meet the specified limits for Endurance.					
Moisture Resistance	After 500 hours storage at +55°C, 90 to 95% R.H., the capacitor shall meet the specified limits for "Endurance".					

#### ■ Dimensions in mm (not to scale)



#### ■ Dimensions in mm (not to scale)

Maximum Oper- ating Voltage (V.DC)	Capacitance (F)	Capacitance range (F)	internal resistance (Ω) at 1kHz	Part number	Min. Packaging QTY (PCS)
5.5	0.022	0.0176 to 0.0396	≦150	EECS0HD 223()	200
	0.047	0.0376 to 0.0846	≦120	EECS0HD 473()	200
	0.10	0.080 to 0.180	≤ 75	EECS0HD 104()	200
	0.22	0.176 to 0.396	≤ 75	EECS0HD 224()	200
	0.33	0.264 to 0.594	≤ 75	EECS0HD 334()	200

<sup>()</sup> Please fill V or H, which means terminal style.