

# PERFECT FIT 3.0

# NPF21-0118N

## CUT-RESISTANT GLOVES

Honeywell Perfect Fit 3.0 gloves are lightweight, fiberglass-free, freefrom silicone, antistatic, touchscreen capable and food certified

### INDUSTRIES

- Automotive industry
- Mechanical and plant engineering
- Metal processing
- Warehousing and logistics
- Production
- Construction
- Transport

### APPLICATIONS

- Paint shop and surface inspection
- Chassis assembly
- Assembly and disassembly
- Maintenance
- Fastening components and parts

We engineered the Honeywell Perfect Fit 3.0 Gloves using advanced technologies and unique features.

The gloves are designed to help workers perform at their best with enhanced comfort, dexterity, grip and protection.

ATTRIBUTE	DESCRIPTION / VALUES
Article No.	NPF21-0118N
Name	Perfect Fit 3.0 NPF21-0118N
Material	Nylon, Carbon, Elastane, PU
Description	Seamless liner, knit wrist, PU palm coating
Sizes	6 -11
Gauge	18
Dexterity	5
Color	Grey liner with black coating
Washable	Yes (3 cycles)
Food certified	Yes
Antistatic	Yes
Touchscreen	Yes
Packing	10 pairs packed in polybag, 10 polybags per case
PPE category	Category II
Certifications	ISO 21420, EN388:2121AASTM D3389, ASTM 2992, FDA 21CFR177.2600 Food Contact Regulation (EC) No. 1935/2004
Classifications	<div>EN 388:2016</div> <div>ASTM F2992</div> <div>ASTM D3389</div> <div>ANSI A1</div> <div>ANSI 2</div> <div>ANSI 2</div> <div>2121A</div> <div>CUT</div> <div>ABRASION</div> <div>PUNCTURE</div>



For More Information  
[automation.honeywell.com](mailto:automation.honeywell.com)

For Information on Innovations and Patents  
[hsmppats.com](mailto:hsmppats.com)

Honeywell Safety Products USA, Inc.  
855 S Mint St, Charlotte, NC 28202

[www.honeywell.com](http://www.honeywell.com)

Honeywell Perfect Fit 3.0 NPF21-0118N Datasheet | 09/2024  
© 2024 Honeywell International Inc.

Honeywell