



auxiliary switch 1 CO for cylindrical fuse base Sz. 22 x 58 mm for monitoring of blown-fuse status of striker-fuses

Model			
product brand name		SETRON	
product designation		auxiliary switches	
design of the product		striker fuses	
design of the product factory mounted		No	
Supply voltage			
operating voltage		250 V	
• rated value			
Switching capacity			
switching capacity current rated value		5 A	
Control current			
type of voltage of control voltage		AC	
Product details			
number of fault signal contacts		0	
number of NC contacts		0	
number of NO contacts		0	
number of CO contacts		1	
product extension can be mounted		others	
product extension		Auxiliary current switch	
Mechanical Design			
height		90 mm	
width		8 mm	
depth		49.8 mm	
number of modular width units		1	
net weight		53 g	
Approvals Certificates			
General Product Approval		Declaration of Conformity	Test Certificates
			other

[Confirmation](#)



[Miscellaneous](#)

[Confirmation](#)

other

[Miscellaneous](#)

#### Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NW7902>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NW7902>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW7902](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7902)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



22 14

13/21

---

last modified:

10/11/2023 

