

Datasheet

Stock No: 1235253

IWR-5 - Five Channel Wireless Receiver



- Pairs with the IWPT/L/U & IWTT/U wireless pressure & temperature transducers
- User-selectable 1-5V or 4-20mA receiver output
- Clean contact output for process, low battery or loss of signal alarm function
- Simple software or DIL switch pairing with IWPT & IWTT transmitters
- Up to 750m range, line-of-sight
- 12 to 32 Vdc powered
- End-to-end accuracy of $\pm 0.25\%$ FS BFSL
- LED indication of wireless link
- DIN rail or wall mounting kits available
- Single channel receiver available - see data sheet 1232522

Description

The IWR-5 is a five channel receiver designed to pair with the IWPT & IWTT wireless pressure & temperature transducers to form a cost effective replacement of traditional wired transducers. This offers a low cost solution to inaccessible or expensive installation environments. The receiver has user selectable voltage or mA outputs corresponding to the calibrated range of the remote Wireless Transducers and 5A rated changeover contacts for alarm functionality.

User channel configuration is possible with the use of the program, IWR-Set, which ensures minimal user set-up time and thus ensures a simple solution to multi-channel pressure & temperature measurement applications. With the standard 0dBi antenna, a line-of-sight range of up to 500m can be achieved and, using the optional 3dBi antenna, up to 750m (LOS) is achievable.

Electrical Protection

Outputs (5 off)	User selectable 1-5V or 4-20mA
Alarm Output (1 off)	5 Amp rated changeover contacts
Receiver Update Rate*	10 seconds as standard. Alternative user settable rates : - 1, 5, 10 and 30 seconds


*Consult IWPT & IWTT Installation manual and data sheet for set-up of alternative transmission rates.

Enclosure Specifications

Dimensions	160 mm x 80 mm x 57 mm
Material*	Light grey ABS (RAL7035)
Protection Class	IP65
Weight	255g inc. 0dBi antenna (+12g with 3dBi)
Installation Position**	Any

* Other materials on request

** Consult Installation Manual to ensure adequate signal path between transmitter and receiver



IWR-5 RS Pro 2016

Specifications are subject to change without prior notice.

Receiver Input

Receiver Frequency*	2.4GHz
System Channel	Standard setting, however user adjustable in multiple instrument systems.
Antenna	Enclosure mounted 0dBi

*Compliant with EN 300 328, V1.8.1

System Performance (@ +20°C)

Accuracy	$\leq \pm 0.25\%$ FS BFSL
Setting Errors (offsets)*	Zero and Full Scale $\leq \pm 0.5\%$ FS

* End-to-end zero tare function available , see user manual.

Instrument Power Source

DC Power	12 to 32Vdc
----------	-------------

Temperature Ratings

Operating Temperature	-10°C to +50°C
Storage Temperature	-20°C to +80°C

Ordering Codes

Transmitters :	See IWPT & IWTT datasheets
Single Channel Receiver:	1232522
Five Channel Configuration Software	Supplied on CD
3dBi Antenna (enclosure mount)	7043335